



## [ PADS & BULK MEDIA ]

### FEATURES

Glasfloss offers a variety of pre-cut pads and bulk media for pre-filter or primary filter applications. Glasfloss pre-cut pads and bulk media come in a variety of fiberglass and 100% non-woven polyester grades that are designed for light to heavy dust loading applications. Standard size pre-cut pads are packaged in a heavy-duty carton that allows quick access and keeps the media clean before installation. Service rolls are available and are packaged in an easy to use cardboard dispenser box.

### CONSTRUCTION

**Fiberglass:** Shall consist of continuous filament fiberglass of graduated density to ensure depth loading and long service life. The air leaving side of the media shall incorporate a skin backing, which supports the media during operation and creates a final filtration stage. The various grades of fiberglass media are engineered for a variety of dust loading applications and shall be treated with a non-toxic, non-flammable, odorless adhesive. The paint arrestor media is engineered for various paint over-spray applications and does not contain adhesive.

**Polyester:** Shall consist of 100% non-woven polyester fibers bonded together. The polyester pre-cut pads and bulk media are engineered for a variety of applications and available in single or multi-ply grades. The polyester pre-cut pads and bulk media are available dry or treated with a non-toxic, non-migratory, odorless adhesive that is incorporated into the filter media.

### APPLICATIONS

The Glasfloss line of pre-cut pads and bulk media offers a variety of options in systems utilizing a permanent frame or holding system. From pre-filters to primary filters, including paint arrestor applications, Glasfloss pre-cut pads and bulk media are proven performers and manufactured to exact specifications to assure consistent performance.



- Progressively Dense Fiberglass or 100% Non-woven Polyester
- Standard and Special Sizes Available
- Skin Backing on Air Leaving Side of Fiberglass
- Service Roll in Easy-to-Use Cardboard Dispenser Box

### SPECIFICATIONS

Media Type	Color	Nominal Thickness	Media Structure	Adhesive	Backing
Commercial	White	1" & 2"	Progressive Density Fiberglass	Light	"Skin"
Paint Arrestor	Green/White	2-1/2"	Progressive Density Fiberglass	-	"Skin"
Hi-Pak	Yellow/White	3"	Progressive Density Fiberglass	Heavy	"Skin"
HL-4	White	1"	Non-Woven Polyester	-	-
HL-8	White	2"	Non-Woven Polyester	-	-
125-4P	Blue/White	5/8"	Non-Woven Polyester	Moderate	-
125-7P	Blue/White	1"	Non-Woven Polyester	Moderate	-
P5T	Green/White	1/2"	Multi-ply Polyester	Moderate	-
P10T	Orange/White	1"	Multi-ply Polyester	Moderate	-
P20T	Orange/White	2"	Multi-ply Polyester	Moderate	-
Hoghair	Blue	1"	Synthetic Fibers	-	-

"Serving You With Locations Throughout The Nation"

Glasfloss has a policy of uninterrupted research, development and product improvement and reserves the right to change design and specifications without notice.

# [ PADS & BULK MEDIA ]

## Pads and Bulk Media Specifications

### COMMERCIAL

- Continuous Filament Fiberglass
- 1" & 2" Nominal Thicknesses Available
- Graduated Density
- Skin Backing
- Moderate Dust Loading Capacity
- 74%-79% Average Arrestance Efficiency
- White Color
- U.L. Class 2

### PAINT ARRESTOR

- Continuous Filament Fiberglass
- 2-1/2" Nominal Thickness
- Graduated Density
- Skin Backing
- High Paint Holding Capacity
- 99.3% Average Removal Efficiency
- Green on Air Entering Side
- U.L. Class 2

### HI-PAK

- Continuous Filament Fiberglass
- 3" Nominal Thickness
- Graduated Density
- Skin Backing
- High Dust Holding Capacity
- Yellow on Air Entering Side
- Non-flammable, Non-toxic Odor Free Adhesive
- 85% Average Arrestance Efficiency
- U.L. Class 2

### HL-4

- 100% Non-woven Polyester
- 1" Nominal Thickness
- Moderate Dust Holding Capacity
- Fire Retarding Bonding Agent
- 82% Average Arrestance Efficiency
- White Color
- U.L. Class 2

### HL-8


- 100% Non-woven Polyester
- 2" Nominal Thickness
- Moderate Dust Holding Capacity
- Fire Retarding Bonding Agent
- 83% Average Arrestance Efficiency
- White Color
- U.L. Class 2

### HOGHAIR

- 100% Synthetic Fibers
- 1" Nominal Thickness
- Interlocking fiber design
- Heavy Dust Holding Capacity
- Cleanable by Vacuuming, Tap Water Rinsing, Hosing or Immersion in a Detergent Solution
- Blue Color
- U.L. Class 2


## STANDARD PRESSURE DROP

Test Filter Size 24" x 24" Nominal



## STANDARD PRESSURE DROP

Test Filter Size 24" x 24" Nominal



## Pads and Bulk Media Specifications

### 125-4P

- 100% Non-woven Polyester
- 5/8" Nominal Thickness
- Graduated Density
- Non-toxic, Non-migratory Adhesive Second Stage
- Light Dust Holding Capacity
- 84% Average Arrestance Efficiency
- White on Air Entering Side
- U.L. Class 2

### 125-7P

- 100% Non-woven Polyester
- 1" Nominal Thickness
- Graduated Density
- Non-toxic, Non-migratory Adhesive Second Stage
- Moderate Dust Holding Capacity
- 86% Average Arrestance Efficiency
- White on Air Entering Side
- U.L. Class 2

### P5T

- 100% Non-woven Polyester
- 1/2" Nominal Thickness
- Fire Retarding Bonding Agent
- Dual Denier Fiber Configuration
- Non-toxic, Non-migratory Adhesive Second Stage
- Moderate Dust Holding Capacity
- 82% Average Arrestance Efficiency
- White on Air Entering Side
- U.L. Class 2

### P10T


- 100% Non-woven Polyester
- 1" Nominal Thickness
- Fire Retarding Bonding Agent
- Dual Denier Fiber Configuration
- Dual Layer Filtration Stages
- Non-toxic, Non-migratory Adhesive Second Stage
- Heavy Dust Holding Capacity
- 92% Average Arrestance Efficiency
- White on Air Entering Side
- U.L. Class 2

### P20T

- 100% Non-woven Polyester
- 2" Nominal Thickness
- Fire Retarding Bonding Agent
- Dual Denier Fiber Configuration
- Dual Layer Filtration Stages
- Non-toxic, Non-migratory Adhesive Second Stage
- Heavy Dust Holding Capacity
- 93% Average Arrestance Efficiency
- White on Air Entering Side
- U.L. Class 2


## STANDARD PRESSURE DROP

Test Filter Size 24" x 24" Nominal



## MINIMUM PARTICLE SIZE EFFICIENCY

Test Filter Size 24" x 24" Nominal



"Serving You With Locations Throughout The Nation"

Glasfloss has a policy of uninterrupted research, development and product improvement and reserves the right to change design and specifications without notice.

**CONSTRUCTION SPECIFICATIONS FOR PADS AND BULK MEDIA**

**Fiberglass:** Shall consist of continuous filament fiberglass of graduated density to ensure depth loading and long service life. The air leaving side of the fiberglass media shall incorporate a skin backing, which supports the media during operation and creates a final filtration stage. The various grades of fiberglass media are engineered for a variety of dust loading applications and shall be treated with a non-toxic, non-flammable, odorless adhesive. The paint arrestor media is engineered for various paint over-spray applications and does not contain adhesive.

**Polyester:** Shall consist of 100% non-woven polyester fibers bonded together. The polyester pre-cut pads and bulk media are engineered for a variety of applications and available in single or multi-ply grades. The polyester pre-cut pads and bulk media are available dry or treated with a non-toxic, non-migratory, odorless adhesive that is incorporated into the filter media.

Distributed by:

