



# 382-386 Summit 3

High Performance, Elongated Front  
Vitreous China, Two-Piece Toilet



Elongated Front



## Features

- Contemporary design
- 1.6 Gpf / 6.0 Lpf
- Wide 2-1/8" glazed trapway
- Large Water Surface
- High performance MagnaFlush II™ flushing technology with 3" flush valve virtually eliminates clogging
- Available in White and Standard Colors: Biscuit and Classic Bone (Consult Price Book for specific colors)
- Model 55 front-mount chrome plated, metal trip lever (Consult Price Book for Additional Finishes)
- Upgrade with a color-match SmartClose™ or Primo™ toilet seat
- Outstanding protection — The Mansfield® limited lifetime warranty

Model 382-386  
shown with SB400  
SmartClose™ toilet seat

Model No.	Description	Approx. Wt.
382-386	Elongated front, (1.6 Gpf/6.0 Lpf) two-piece toilet. Features 3" flush valve and 2-1/8" trapway. Includes tank trim and front-mount chrome plated, metal trip lever. Less toilet seat and supply. Specify color.	84 lbs. (38 kg)
382	Elongated front toilet bowl only. 12" rough-in. Less toilet seat. Specify color.	50 lbs. (23 kg)
386	Tank and cover only, with left hand, front-mount chrome plated, metal trip lever. Less supply. Specify color.	34 lbs. (15 kg)
SB400	Elongated, SmartClose™ toilet seat. Specify color.	5.5 lbs. (2 kg)
SB1200	Elongated, Primo™ toilet seat. Specify color.	5.5 lbs. (2 kg)



**MagnaFlush II™**

382-386

# Summit 3

High Performance, Elongated Front  
Vitreous China, Two-Piece Toilet

## Features & Upgrades

### MagnaFlush™ Flushing Technology

Featuring an extra-large 3" flush valve, a pilot operated fill valve and our glazed 2-1/8" trapway. MagnaFlush II™ flushing technology offers a fast and powerful flush — every time. Ideal for residential and commercial use. MagnaFlush II™ — Performs Without Compromise.

**MagnaFlush II™**

### 206-1212 Flush Valve

Our newest 3" flush valve features a high volume flow rate for a quick and quiet flush action. Designed for maximum performance, it offers more than twice the potential flow rate of a conventional two-inch flush valve. Non-corrosive and durable, it will provide years of dependable use.



### 2206 Pilot Operated, Anti-Siphon Fill Valve

The 2206 fill valve operates efficiently at low or high water pressures. Featuring a patented flow regulator and debris filter and positive shut-off for added functionality. Easily adjustable to retain optimum water level.



### Add a Toilet Seat

With a simple touch, Mansfield's newest SmartClose™ toilet seat closes gently and quietly. Or upgrade your toilet with a popular Primo™ toilet seat. Made of durable, high impact, heavy-duty plastic. For all applications — Get More, Get Mansfield®.




## Technical Information

### Specifications

Material	Vitreous China
Water Pressure Range	20 to 80 P.S.I.
Flush System	MagnaFlush II™ Flushing Technology
Water Usage	1.6 Gpf / 6.0 Lpf
Water Surface Area	10" x 8"
Trap Diameter	2-1/8"
Trap Seal	2-1/2"
Rough-in	12"
Shipping Dimensions	Model 382 27-1/2" x 15-7/16" x 15-1/8" (699 mm x 392 mm x 384 mm) Model 386 19-1/2" x 9-7/8" x 15-3/4" (495 mm x 251 mm x 400 mm)
Shipping Weight	Model 382 - 53 lbs (24 kg) Model 386 - 36 lbs (16 kg)
Warranty	Vitreous China - Limited Lifetime Tank Trim - Limited One Year

These dimensions are nominal and are subject to change without prior notice.

Fixture performance and specifications meet or exceed, ANSI/ASME A112.19.2 standards and CAN/CSA B45.0 standards, and other state and local codes.



NOTE: Install this product according to the installation guide.

Fixture dimensions are nominal and conform to tolerances in ASME Standard A112.19.2

See our complete line of acrylic and vitreous china bathroom fixtures, plastic tank trim and plumbing products.



Mansfield Plumbing Products LLC • Customer Service Toll Free 877-850-3060 • Fax 419-938-6234  
Website: [www.mansfieldplumbing.com](http://www.mansfieldplumbing.com) • Email: [custserv@mansfieldplumbing.com](mailto:custserv@mansfieldplumbing.com)

Form No. M382386 Printed in U.S.A. 7/09  
© 2009 Mansfield Plumbing Products LLC