





P.O. Box 3365 South El Monte, CA 91733 626.444.0541 Fax 626.444.3887 www.Afcon.org

078

TRANSITION FITTING LOCKING



SIZE - BRACE PIPE - 1" and 1 1/4" Sch. 40
MATERIAL - Carbon Steel or S.S. (Type 304).
FINISH - Plain or E.G.
LISTING/APPROVAL -



203A-EX 2625

Listed only for use with other **AFCON** bracing products.

FM Approved

OSHPD OPA-0601-07 See Website.

FUNCTION - Adapts the sway brace fitting to the brace pipe in an **AFCON** sway brace assembly. Sway brace assemblies are intended to be installed in accordance with NFPA 13 and the manufacturer's installation instructions.

Common component in an AFCON longitudinal sway brace - see drawing.

INSTALLATION - Per these instruction including NFPA 13 and 13R.

Load rating - see chart.

The required type, number and size of fasteners used to structure attachment fitting shall be in accordance with NFPA 13.

DO NOT BEND - If angle required use part #070, #076 or #077.

ASSEMBLY

Combine with proper **AFCON** components.

Insert brace pipe into fitting against the pivot bolt .

Tighten set bolt until head contacts bracket.

FEATURES

* Visual inspection, verifies proper installation.

* Bolt hole fits #410/411 sway brace fitting.

ORDERING - Part #, pipe size and finish.

Horizontal Load Ratings		
Size	FM	UL LISTED
1 - 1 1/4	1200	2015

Specific **AFCON** products are exclusively designed to be compatible **ONLY** with other **AFCON** products including parts and fasteners, resulting in a listed sway brace, restrainer or hanger assembly. **Be advised** the following warranty restriction will apply. **DISCLAIMER** - **AFCON** will **NOT** warrant against the failure of its products when used in combination with other products, parts or systems not manufactured or sold by **AFCON**. **AFCON** shall **NOT** be liable under any circumstances whatsoever for any direct or indirect, incidental or consequential damages of any kind, including but not limited to loss of business or profit, when non-**AFCON** products have been, or are used.

