



Short Floor-to-Vent Heights

Small Jacket Diameters

Greater Installation Flexibility







# Available in 60, 75 and 100 Gallon Tank-Type Model

## ▶ 50,000 BTU/Hr. thru 80,000 BTU/Hr.

Rheem-Ruud gas commercial water heaters are specifically designed to fill the need wherever medium quantities of hot water are required. Typical applications include small restaurants, apartments and small office buildings.

## **Construction Features:**

- Space saving design short heights and small jacket diameters result in greater installation flexibility.
- Long life tank design proprietary steel formulation with a unique coat of high temperature porcelain enamel to maximize corrosion resistance resulting in a superior tank design. Dual magnesium anode rods are installed for longer tank life.
- Foam insulation rigid foam insulation provides superior insulating qualities, improves efficiency and reduces operating costs. Our patented process of injecting foam into the insulating cavity adds additional durability and dent resistance to the heater jacket.

#### • Automatic controls -

control system is designed to shut off gas if the pilot flame is extinguished. Relighting is a safe, easy procedure. Thermostat settings to 160°F. A built-in gas pressure regulator assures even gas flow.

- Temperature and pressure relief valve – AGA/ASME rated and factory installed.
- Full port, full flow brass drain valve

## **Certifications and Ratings:**

- Efficiency these models have been tested according to DOE test procedures, and meet or exceed the thermal efficiency and standby loss requirements of current ASHRAE standards (Part of the Federally mandated Energy Policy Act (EPact)). Also exceeds energy efficiency codes of all states including California Energy Commission (CEC).
- Safety and construction these products are design certified by CSA Laboratories: a) For operation at 160°F. b) To meet all safety and construction requirements of ANSI Z21.10.1/ANSI Z21.10.3.
  c) As an automatic storage water heater. d) For operation of combustible floors and alcove installations. e) For combination water heating and space heating applications. All models are North Carolina and Massachusetts Code compliant. Certified for a 150 PSI Maximum Working Pressure.

<b>RECOVERY CAPACITIES</b> Recovery in U.S. Gallons/Hr. (GPH) at various temperature rises											
MODEL NUMBER	INPUT (BTU/HR.)	40°F	50°F	60°F	70°F	80°F	90°F	100°F	110°F	120°F	130°F
G60-50N	50,000	115	92	77	66	58	51	46	42	38	35
G60-50LP	45,000	104	83	69	59	52	46	41	38	35	32
G75-75N-2	75,100	182	146	121	104	91	91	73	66	61	56
G75-75LP	65,000	158	126	105	90	79	70	63	57	53	48
G100-80	80,000	194	155	129	111	97	86	78	71	65	60
G100-80N	76,000	184	147	123	105	92	82	74	67	61	57

Recovery rating is based on recovery efficiencies obtained in a CSA certified laboratory. N = Low NOx

MAXIMUM DELIVERY Delivery in U.S. Gallons. (Includes useable storage and recovery for indicated times)														
MODEL NUMBER	GALLON Capacity	INPUT (BTU/HR.)	TEMP. Rise	UNITS	5 Min.	10 Min.	15 Min.	20 Min.	30 Min.	45 Min.	60 Min.	120 Min.	180 Min.	Min. to Rec. Contents
G60-50N	60	50,000	100 °F	GAL	46	50	54	57	65	77	88	134	180	78
G60-50LP	60	45,000	100 °F	GAL	45	49	52	56	63	73	84	125	166	87
G75-75N-2	75	75,100	100 °F	GAL	59	65	71	77	89	107	125	198	271	62
G75-75LP	75	65,000	100 °F	GAL	57	63	68	74	84	100	116	179	242	71
G100-80	100	80,000	100 °F	GAL	77	83	89	96	109	128	148	225	303	77
G100-80N	100	76,000	100 °F	GAL	76	82	88	95	107	125	144	217	291	81

### DIMENSIONAL INFORMATION

MODEL			D	0		-	-	•	CLEARANCE TO COMBUSTIBLES		APPROX. Shipping	
NUMBER	UNITS	A	B	U	U	E	F	G	SIDE	FRONT	TOP	WEIGHT
G60-50	inches	62	58	23	13-1/4	4	8	48-1/2	1	3	2	180 lbs
G75-75	inches	64	60	26-1/4	13-1/4	4	11	53-1/4	1	3	2	320 lbs.
G100-80	inches	69-5/8	65-3/4	28-1/4	11	4	15	57-13/16	1	Alcove	12	410 lbs.


## **Recommended Specifications:**

Water heater(s) shall be model \_\_\_\_\_\_ manufactured by RHEEM-RUUD, having gas input of \_\_\_\_\_\_ Btu/hr. and a recovery rate of \_\_\_\_\_ GPH at a 100°F temperature rise. Water heater(s) shall have a storage capacity of


gallons. Water heater(s) shall have the AGA seal of certification and be factory equipped with an AGA/ASME rated temperature and pressure relief valve. Tank(s) shall have a coating of high temperature porcelain enamel and furnished with a magnesium anode rod rigidly supported and a full port, full flow brass drain valve. Water heater(s) shall meet or exceed the energy factor requirements of ASHRAE. Tanks shall have a working pressure rating of 150 psi, and shall be completely factory assembled, including a pressure regulator properly adjusted gas. Controls will for operation on be arranged for safety shutoff in event of pilot failure. Complete unit shall be insulated with rigid polyurethane foam insulation. Water heater(s) shall be covered by a three year limited warranty against tank leaks.

#### **Limited Warranty:**

This product features a three year limited warranty against tank leaks. Please refer to Commercial Warranty Information brochure for complete warranty information.



G60-50 & G75-75 SIDE TAPS ON 75 GAL. MODEL ONLY G60-50 WATER CONNECTIONS ARE 3/4" NPT G75-75 WATER CONNECTIONS ARE 1" NPT





In keeping with its policy of continuous progress and product improvement, Rheem-Ruud reserves the right to make changes without notice.

Rheem Water Heating • 101 Bell Road, Montgomery, Alabama 36117-4305 • www.rheem.com