## **ROD ATTACHMENTS**



## Fig. 157

## **Extension piece**

Size Range: <sup>3</sup>/<sub>8</sub>" through <sup>7</sup>/<sub>8</sub>" Material: Malleable iron Finish: ☐ Plain or ☐ Galvanized Maximum Temperature: 450° F

**Service:** For attaching hanger rod to various types of building

attachments.

**Approvals:** UL Listed (3/8" - 7/8" rod size) and FM Approved (3/8" &

1/2" rod size).

**Installation:** May be used to form an integral part of malleable

iron beam clamps Fig. 218, see page 52.

**Ordering:** Specify rod size, figure number, name and finish.




FIG. 157: LOADS (LBS) • WEIGHTS (LBS) • DIMENSIONS (IN)								
Rod Size A	Max Load	Weight	В	C	Rod Take-Out – E	G	Н	K
3/8	730	0.20	11/4	21/16	11/4	1/2	1/2	9/16
1/2	1,350	0.40	1%	25/16	13/8	5/8		11/16
5/8	1,550	0.44	1½	27/16	17/16			3/4
3/4	2,100	0.65	13/4	27/8	111/16			7//8
7/8	2,350	0.78	17/8	2	13/4	3/4		

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	☐ Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	