






HVAC CONDENSATE REMOVAL SYSTEM

Series Specifications

- Low profile for limited space applications
- ABS tank, motor cover and volute
- 3/10 gal tank capacity
- Stainless steel shaft
- Removable 3/8" (9.5 mm) barbed check valve
- Thermal overload protection
- Safety switch
- 6' power cord with 3-prong molded plug

PSCP20LPWS



Item Number	Volts	Hertz	Amps	Watts	Gallons/Liters Per Hour at Height			Cord	Shutoff	Weight lbs/kg
					1' .3 m	3' .9 m	15' 4.6 m			
PSCP20LPWS	115	60	1.5	93	80 gph 303 lpm/5.0 lpm	70 gph 265 lpm/5.0 lpm	25 gph 95 lpm/1.6 lpm	6' 1.8m	20' 6.1m	5.4 2.5

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.
This product is NSF/ANSI Std. 61 compliant

