Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No
Approval	Representative

# Colt<sup>™</sup> Series C300 (Colt 300), C300N (Colt 300N)

### **Double Check Detector Assemblies**

### Sizes: 2½" – 10"


The Colt C300, C300N Double Check Detector Assemblies are designed to protect drinking water supplies from dangerous crossconnections in accordance with national plumbing codes and water authority requirements for non-potable service applications such as irrigation, fire line, or industrial processing. The Colt C300, C300N may be installed under continuous pressure service and may be subjected to backpressure for non-toxic applications. The Colt C300, C300N is used primarily on fire line sprinkler systems when it is necessary to monitor unauthorized use of water. For use in non-health hazard applications.

#### **Features**

- Extremely Compact Design
- 70% Lighter than Traditional Designs
- 304 (Schedule 40) Stainless Steel Housing & Sleeve
- Groove Fittings Allow Integral Pipeline Adjustment
- Patented Tri-Link Check Provides Lowest Pressure Loss
- Unmatched Ease of Serviceability
- Available with Grooved Butterfly Valve Shutoffs
- May be Used for Horizontal, Vertical or N Pattern Installations
- Replaceable Check Disc Rubber

#### Specifications

The Colt C300, C300N Double Check Detector Assemblies shall consist of two independent Tri-Link Check modules within a single housing, sleeve access port, four test cocks and two drip tight shutoff valves. Tri-Link Check shall be removable and serviceable, without the use of special tools. The housing shall be constructed of 304 (Schedule 40) stainless steel pipe with groove end connections. Tri-Link Checks shall have reversible elastomer discs and in operation shall produce drip tight closure against the reverse flow of liquid caused by backpressure or backsiphonage. The bypass assembly shall consist of a meter, which registers in either gallon or cubic measurement, a double check valve assembly and required test cocks. Assembly shall be a Colt C300, C300N as manufactured by the Ames Fire & Waterworks.



#### A WARNING

It is illegal to use this product in any plumbing system providing water for human consumption, such as drinking or dishwashing, in the United States. Before installing standard material product, consult your local water authority, building and plumbing codes.

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Ames Fire & Waterworks product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Ames Fire & Waterworks Technical Service. Ames Fire & Waterworks reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Ames Fire & Waterworks products previously or subsequently sold.

A WATTS Brand

### Configurations

- Horizontal
- Vertical up
- "N" pattern horizontal

### **Materials**

- Housing & Sleeve: 304 (Schedule 40) Stainless Steel
- Elastomers: EPDM, Silicone and Buna 'N'
- Tri-Link Checks: Noryl<sup>®</sup>, Stainless Steel
- Check Discs: Reversible Silicone or EPDM
- Test Cocks: Bronze Body Nickel Plated
- Pins & Fasteners: 300 Series Stainless Steel
- Springs: Stainless Steel

### Dimensions – Weights

### **Available Models**


Suffix:

- OSY UL/FM outside stem and yoke resilient seated gate valves
- BFG UL/FM grooved gear operated butterfly valves with tamper switch
- \*OSY FxG Flanged inlet gate connection and grooved outlet gate connection
- \*OSY GxF Grooved inlet gate connection and flanged outlet gate connection
- \*OSY GxG Grooved inlet gate connection and grooved outlet gate connection

Available with grooved NRS gate valves — consult factory\* Post indicator plate and operating nut available — consult factory\* \*Consult factory for dimensions


#### **Pressure – Temperature** Temperature Range: 33°F – 140°F (0.5°C – 60°C)


Temperature Range: 33°F – 140°F (0.5°C – 60°C) Maximum Working Pressure: 175psi (12.1 bar)



#### C300, C300N

SIZE	DIMENSIONS															WEIGHT				
	A		C (0SY)		D		G		Н		I		J		Р		C300		C300N	
in.	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.	lbs.	kgs.
<b>2</b> <sup>1</sup> / <sub>2</sub>	30¾	781	16¾	416	31/2	89	<b>29</b> <sup>1</sup> /16	738	<b>21</b> ½	546	15½	393	<b>8</b> <sup>13</sup> ⁄16	223	133/16	335	139	63	147	67
3	31¾	806	181/8	479	311/16	94	301/4	768	221/4	565	171//8	435	<b>9</b> <sup>3</sup> ⁄16	233	141/2	368	159	72	172	78
4	33¾	857	<b>22</b> <sup>3</sup> ⁄4	578	4	102	33	838	231/2	597	<b>18</b> ½	470	<b>9</b> <sup>15</sup> /16	252	153/16	386	175	79	198	90
6	431/2	1105	301/%	765	51/2	140	443⁄4	1137	331/4	845	<b>23</b> <sup>3</sup> ⁄16	589	131/16	332	19	483	309	140	350	159
8	49¾	1264	37¾	959	611/16	170	541/8	1375	401/8	1019	277/16	697	15 <sup>11</sup> /16	399	<b>21</b> <sup>3</sup> ⁄16	538	494	224	569	258
10	57¾	1467	<b>45</b> ¾	1162	<b>8</b> <sup>3</sup> ⁄16	208	66	1676	<b>49</b> ½	1257	<b>32</b> ½	826	175/16	440	24	610	795	361	965	438





#### C300BFG, C300NBFG

SIZE			DIMENSIONS														WEIGHT			
	A		С		D		G		Н		I		J		Р		C300BFG		C300NBFG	
in.	in.	тт	in.	тт	in.	mm	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.	lbs.	kgs.
<b>2</b> <sup>1</sup> / <sub>2</sub>	273⁄4	705	8	203	31/2	89	297/8	759	<b>21</b> ½	546	<b>14</b> <sup>15</sup> / <sub>16</sub>	379	<b>8</b> <sup>13</sup> /16	223	13	330	70	32	78	35
3	281/4	718	85/16	211	311/16	94	<b>30</b> <sup>11</sup> /16	779	221/4	565	157/16	392	<b>9</b> <sup>3</sup> ⁄16	233	131/2	343	68	31	81	37
4	29	737	<b>8</b> <sup>15</sup> ⁄16	227	311/16	94	<b>31</b> <sup>15</sup> ⁄16	811	231/2	597	16¼	412	<b>9</b> <sup>15</sup> /16	252	14	356	75	34	98	44
6	361/2	927	10	254	5	127	433/16	1097	331/4	845	<b>19</b> <sup>11</sup> / <sub>16</sub>	500	<b>13</b> <sup>1</sup> ⁄16	332	141/2	368	131	59	171	78
8	<b>42</b> <sup>3</sup> ⁄4	1086	12¼	311	61⁄2	165	<b>51</b> <sup>1</sup> ⁄16	1297	401/%	1019	235/16	592	<b>15</b> <sup>1</sup> / <sub>16</sub>	399	<b>18</b> <sup>3</sup> ⁄16	462	275	125	351	159

Noryl<sup>®</sup> is a registered trademark of SABIC Innovative Plastics<sup>™</sup>.

### Approvals

- Approved by the Foundation for Cross-Connection Control and Hydraulic Research at The Unversity of Southern California (FCCCHR-USC)
- AWWA C510-97

Horizontal

For additional approval information please contact the factory or visit our website at www.amesfirewater.com




### Capacity


UL/FM Certified Flow Characteristics Flow characteristics collected using butterfly shutoff valves.


## Flow capacity chart identifies valve performance based upon rated water velocity up to 25fps


- Service Flow is typically determined by a rated velocity of 7.5fps based upon schedule 40 pipe.
- Rated Flow identifies maximum continuous duty performance determined by AWWA.
- UL Flow Rate is 150% of Rated Flow and is not recommended for continuous duty.
- AWWA Manual M22 [Appendix C] recommends that the maximum water velocity in services be not more than 10fps.





Vertical \_\_\_\_\_ N - Pattern











**NOTICE** Inquire with governing authorities for local installation requirements



A WATTS Brand

 USA: Backflow
 Tel: (978) 689-6066 • Fax: (978) 975-8350 • AmesFireWater.com

 USA: Control Valves
 Tel: (713) 943-0688 • Fax: (713) 944-9445 • AmesFireWater.com

 Canada:
 Tel: (905) 332-4090 • Fax: (905) 332-7068 • AmesFireWater.ca

 Latin America:
 Tel: (52) 81-1001-8600 • AmesFireWater.com

© 2018 Ames Fire & Waterworks