


# Reciprocating Saw Bi-Metal Blades



<b>Model Numbers</b>	<b>Length</b>	<b>Teeth per inch (TPI)</b>	<b>Recommended for cutting:</b>
<b>RAPRB156</b>	12	6	Wood with Nails, General Roughing In
<b>RAPRB656</b>	6	6	Wood with Nails, General Roughing In
<b>RAPRB956</b>	9	6	Wood with Nails, General Roughing In
<b>RAPRB610</b>	6	10	Wood, Plastic & Steel
<b>RAPRB810</b>	8	10	Wood, Plastic & Steel
<b>RAPRB110</b>	12	14	Metal 3/16" thru 1/4"
<b>RAPRB614</b>	6	14	Metal 3/16" thru 1/4"
<b>RAPRB618</b>	6	18	Metal 1/8" thru 3/16"
<b>RAPRB818</b>	8	18	Metal 1/8" thru 3/16"
<b>RAPRB624</b>	6	24	Metal thinner than 1/8"

## Product Features

- Bi-metal design
- Long lasting
- Fast cuts
- Latest tooth geometry

6 TPI	10TPI	14TPI	18TPI	24TPI
WOOD				
PLASTER (w/ mesh and lath)				
GENERAL DEMOLITION (wood and nail embedded wood)				
PLASTICS AND COMPOSITES				
	METAL - 1/8" to 1/2" thick			
	METAL - 3/32" to 5/16" thick			
	METAL - 1/8" or less thick			

**Warranty**  
1-year against manufacturer's defects.

**Defectives**  
Please use branch defective allowance and field destroy all defective material.