## **BrassCraft**®

## Gas Ball Valves

Experience the Difference in Quality, Performance & Product Innovation





BrassCraft Manufacturing's exclusive line of Italian-made gas ball valves are specially engineered to provide unsurpassed product performance. From the stem to the body to the exclusive handle design, every detail has been master crafted for ease of operation and installation. Each BrassCraft® gas ball valve is manufactured to the industry's highest standards for consistent product quality and superior performance.



Available in a variety of configurations for use with natural, manufactured, mixed, liquefied-petroleum gases, and LP gas-air mixtures.

## • FORGED BRASS BODY

Eliminates pinhole leaks commonly associated with cast products

### • PTFE SEAT RINGS

Assures a tight seal and easy on & off operation even after long periods of inactivity

#### BLOW-OUT PROOF STEM

Assembled from the inside with double o-ring protection to ensure safe, reliable performance

- 1/4-TURN OPERATION
  Provides easy on & off flow control
- COMFORT-FIT GRIP

An exclusive integration of the 'T' and lever handle designs

- LARGE WRENCH FLATS
  Makes installation easier
- 100% LEAK TESTED
- CSA CERTIFIED



For more details, or to place an order, contact your local BrassCraft Mfg. sales or customer service representative.

Part			Valve Dimensions (IN)			Flow Rate	Pack	Master Carton	
	No.	Part Description	*D	Н	L	M	SCFH	Qty	Qty
FIP x FIP									
M	TBV8	1/2" FIP x 1/2" FIP	0.39	1.45	2.22	1.30	150,000	10	50
	TBV12	3/4" FIP x 3/4" FIP	0.59	1.70	2.63	1.30	400,000	10	50
	TBV16	1" FIP x 1" FIP	0.79	1.83	2.58	1.30	670,000	6	36

	Part		Valve Dimensions (IN)			**Capacity	Pack	Master Carton	
	No.	Part Description	*D	Н	L	М	Btu/Hr (Watts)	Qty	Qty
FULL PORT - FIP x FIP									
H D D	TBV12F	3/4" FIP x 3/4" FIP, Full Port 425 WOG	0.79	1.79	2.54	1.30	750,000 (219,802)	6	50
FLARE x FIP									
	TBV6-8	3/8" OD Tube x 1/2" FIP	0.28	1.45	2.30	1.30	50,000 (14,654)	10	50
M — M —	TBV6F-8	3/8" OD Tube (9/16 -24 Fine Thread) x 1/2" FIP	0.28	1.45	2.30	1.30	50,000 (14,654)	10	50
	TBV8-8	1/2" OD Tube x 1/2" FIP	0.39	1.45	2.41	1.30	100,000 (29,307)	10	50
-D	TBV10-8	5/8" OD Tube (15/16 -16 Thread) x 1/2" FIP	0.51	1.50	2.50	1.30	100,000 (29,307)	10	60
	TBV10-12	5/8" OD Tube (15/16 -16 Thread) x 3/4" FIP	0.51	1.50	2.50	1.30	130,000 (38,099)	10	60
M I	TBVA6-8	3/8" OD Tube x 1/2" FIP	0.28	1.70	1.88	1.30	50,000 (14,654)	10	60
	TBVA8-8	1/2" OD Tube x 1/2" FIP	0.39	1.70	1.88	1.30	100,000 (29,307)	10	60
ANGLE	TBVA10-12	5/8" OD Tube (15/16 -16 Thread) x 3/4" FIP	0.51	1.70	2.00	1.30	130,000 (38,099)	10	60
FLARE x FLARE									
M —	TBVF6	3/8" OD Tube x 3/8" OD Tube	0.28	1.45	2.46	1.30	50,000 (14,654)	10	50
	TBVF8	1/2" OD Tube x 1/2" OD Tube	0.39	1.45	2.74	1.30	100,000 (29,307)	10	50

- \* D = Minimum diameter of gas pathway through valve
- \*\* Capacity is determined with .64 specific gravity gas with energy content of 1000 Btu/Cubic Foot (37.7 MJ/M3) at .3 inches water column (75 Pa) pressure drop. Capacities stated above are minimum capacities allowed by ANSI Z21.15 CSA 9.1. BrassCraft® valves meet or exceed these requirements.

#### **Material Specifications:**

Body - Forged brass Retainer - Forged brass

Ball - Chromium-plated brass

Seats - PTFE

Stem - Extruded brass

O-ring - Viton® (high temperature rubber)\*

Handle - Aluminum Screw - Zinc-plated steel

Viton® is a registered trademark of DuPont Dow Elastomers, L.L.C..

# Design-Certified & Manufactured Working Pressure / In Accordance With: Operating Temperature ANSI Z21.15 - CSA 9.1 1/2 PSI (32°F to 125°F) CGA CR91-002 5 PSI (-40°F to 125°F) ANSI / ASME B16.44 5 PSI (32°F to 125°F)

## Committed to Quality, Driven by Innovation.



**BrassCraft**®





BrassCraft Manufacturing Co. 39600 Orchard Hill Place Novi, Michigan 48375-5331 TOLL-FREE: (877) 272-7755 FAX: (248) 305-6011

350 South Edgeware Road St.Thomas, Ontario Canada N4P 4C4 TOLL-FREE: (800) 265-4322 FAX: (800) 567-9100

For Residential and Commercial Applications					
Job Name		Engineer / Architect			
Job Location		Wholesaler			
Submittal Date		Contractor			

## TBVA Series Angle Gas Ball Valve - Flare x Female Iron Pipe

Use: For use with natural, manufactured, mixed, liquefied-petroleum (LP) gas, and LP gas-air mixtures.

Note: The National Fuel Gas Code requires a gas shut-off valve installed upstream, within "easy reach" or 6 feet of the gas appliance


### **Design Features:**

- Heavy duty, forged brass body eliminates pinhole leaks commonly associated with cast products
- Blow-out proof stem is assembled from the inside with double o-rings for reliable performance
- PTFE seat rings for longer life and consistent performance
- Right-sized handles ensure on/off operation even in tight installations
- Quarter turn operation for easy on/off flow control
- Approved for indoor/outdoor use
- 100% Leak tested

## **Operating Specifications:**

**Temperature:** -40° - 150° F **Pressure:** 5 PSI maximum

VALVE MATERIAL SPECIFICATIONS				
<b>Body</b> Forged brass				
Retainer	Forged brass			
Ball	Brass, chrome plated			
Seat	PTFE			
Stem	Brass			
O-ring High-temperature rubber				
Handle	Aluminum			
Screw	Steel, zinc plated			






## TBVA Series Angle Gas Ball Valve - Flare x Female Iron Pipe

## Part Listing:

☐ TBVA6-8☐ TBVA8-8☐ 3/8" OD flare x 1/2" FIP, angle☐ 1/2" OD flare x 1/2" FIP, angle

TBVA10-12 5/8" OD flare (15/16-16 thread) x 3/4" FIP, angle



PART SPECIFICATIONS (Inches)						
Model	DIM. A	DIM. B	DIM. C	DIM. D		
TBVA6-8	1.89	1.21	1.21	1.70		
TBVA8-8	1.89	1.21	1.45	1.70		
TBVA10-12	2.00	1.31	1.51	1.70		

### **Country of Origin:**

Made in Italy

## **Listings and Certifications:**

• CSA listed to ANSI Z21.15 / CSA 9.1, ANSI / ASME B16.44, and CGA CR91-002



