




TRI-FLOW® INDUSTRIAL LUBRICANT FOOD GRADE ANTI-SEIZE TF23015, TF23016, TF23017



- NSF Registered, H1 rated
- Protects to 1800°F
- Leak proof seal
- Kosher approved
- Formulated with P.T.F.E.
- Prevents galling & seizing
- Non-Melting
- Chemical & steam resistant



CLEANERS, DEGREASERS
LUBES AND SEALANTS

SUPERIOR
LUBRICANTS

PAINTS, COATINGS
AND PRIMERS

CAULKS, SEALANTS
AND ADHESIVES

BRUSHES, ROLLER COVERS
AND ACCESSORIES

Tri-Flow® Industrial Lubricant Food Grade Anti-Seize is a premium, synthetic, non-drying thread sealant and anti-seize compound. Formulated with a balanced blend of P.T.F.E. and other lubricating solids, homogenized into a non-melting grease carrier. It is NSF registered, H1 rated, and Kosher approved which gives full acceptability for use in all areas where incidental food contact may occur. Tri-Flow Food Grade Anti-Seize is engineered to provide a superior leak-proof seal for the life of the connection; while at the same time maintaining its anti-seize capabilities, allowing easy assembly without thread damage. Tri-Flow Anti-Seize brush-top products do not contain any solvents, lead, graphite or clay fillers. It meets Mil-A-907E requirements.



TF23015
9 oz. Jar

TF23016
18 oz. Jar

TF23017
11.25 oz. Aerosol



PHYSICAL PROPERTIES AEROSOL

APPEARANCE: White
BASE: Synthetic w/P.T.F.E.
ODOR: Slight Solvent
LABEL WEIGHT: 11.25 oz.
PROPELLANT: Hydrocarbon
WT/GAL: 6.22 lbs.
SPECIFIC GRAVITY: 0.75
% NON VOLATILE: 36.0%
% VOC: 64.0%
SHELF LIFE: 3 years from date of manufacture
NSF RATING: See Chart
FLASH POINT: > 0°F
HMIS (NFPA RATING): 2, 4, 0

PHYSICAL PROPERTIES BULK

APPEARANCE: Off-White Semi-Solid
BASE: Synthetic w/P.T.F.E.
ODOR: Low Odor
LABEL WEIGHT: 9 oz and 18 oz. Brush-Top
SPECIFIC GRAVITY: 1.18
% VOC: 0
MEETS: MIL-A-907E
N.L.G.I. RATING: 1
FLASH POINT: 400°F per ASTM D-92
NSF RATING: See Chart
SHELF LIFE: 3 years from date of manufacture
HMIS (NFPA RATING): 1, 1, 1
OPERATING TEMPERATURE: 1800°F
POUR POINT: 5°F per ASTM D-97

USES

- Brass
- Galvanized steel
- Aluminum
- Fiberglass reinforced pipes
- Black iron
- Stainless steel
- Copper
- PVC

CAUTION: Not recommended for oxygen service.

APPLICATION

Maximum performance is achieved when the metal surfaces to be protected are clean, dry and free of rust, oil and mill scale.

Aerosol Application:

- Product should be sprayed in a well ventilated area.
- Sprays best at room temperature
- Shake well before using
- Spray at a distance of 10" to 14" from surface.

PACKAGING

Stock No.	Description	UPC Code	NSF Reg. #	NSF Rating	Case Pack
TF23015	9 oz. Jar	0-32053-23015-8	128182	H1	12
TF23016	18 oz. Jar	0-32053-23016-5	128182	H1	12
TF23017	Aerosol	0-32053-23017-2	129462	H1	12

RESOURCES

MSDS/EDS/PRODUCT DATA
SHEETS: www.paintdocs.com
CUSTOMER SERVICE:
 1-800-777-2966
TECHNICAL INFORMATION:
 1-800-251-2486

**EVERYTHING ELSE
IS JUST A LUBE!**

Distributed By:



INDUSTRIAL

Krylon Products Group
 101 Prospect Ave. NW
 Cleveland, OH 44115
www.KPG-Industrial.com
 Tel: 1-800-777-2966