


- Longer Life
- Patented magnesium anode rod design incorporates a special resistor that protects the tank from rust
- \*See Residential Warranty Certificate for Energy Factor and Average Annual Operating Costs based on D.O.E. (Department of Energy) test procedures. D.O.E. national average fuel rate natural gas \$1.218/therm; LP \$1.87/gallon.



|                  | DESCRIPTION      |              |             | FEATURES |   |      |                         |                                   | ROUGHING IN DIMENSIONS (SHOWN IN INCHES) |                  |            |                             |                   |                              |                            |                     |                       | ENERGY INFO.             |                                 |
|------------------|------------------|--------------|-------------|----------|---|------|-------------------------|-----------------------------------|--|------------------|------------|-----------------------------|-------------------|------------------------------|----------------------------|---------------------|-----------------------|--------------------------|---------------------------------|
| T<br>Y<br>P<br>E |                  | GAL.<br>CAP. |             |          | GAS INPUT IN<br>Thous. Btu/hr.<br>Nat. LP |      | ERY IN<br>0° RISE<br>LP | FIRST HOUR<br>Del. G.P.H.<br>Nat. | HT. TO<br>VENT<br>A                      | TANK<br>HT.<br>B | DIAM.<br>C | HT. TO<br>GAS<br>CONN.<br>D | VENT<br>SIZE<br>E | WATER<br>CONN.<br>CNTR.<br>F | HT. TO<br>SIDE<br>T&P<br>G | WATER<br>CONN.<br>H | SHIP.<br>WT.<br>(LBS) | ENERGY<br>FACTOR<br>NAT. | AVG. ANN.<br>OPER. COST<br>NAT. |
|                  |                  | 40           | 42VR40-40F  | 40       | 34  | 40.4 | 34.3                    | 68                                | 63-1/4                                   | 59-3/4           | 21         | 14-1/2                      | 3                 | 8                            | 53-1/2                     | 3/4                 | 135                   | 0.62                     | \$294                           |
|                  | IALL             | 50           | 42VR50-40F  | 40       | 36  | 40.4 | 36.4                    | 83                                | 62-1/4                                   | 58-3/4           | 23         | 14-1/2                      | 3                 | 8                            | 52-1/2                     | 3/4                 | 165                   | 0.62                     | \$294                           |
|                  | T<br>A<br>L<br>L | 29           | 22V30F      | 32       | 30  | 32.3 | 30.3                    | 50                                | 59-3/4                                   | 56-3/8           | 16-1/8     | 14-1/2                      | 3                 | 8                            | 50-3/4                     | 3/4                 | 100                   | 0.62                     | \$294                           |
|                  |                  | 40           | 22V40-36F1  | 36       | -   | 36.4 | -                       | 67                                | 61-1/2                                   | 58               | 17-3/4     | 14-1/2                      | 3                 | 8                            | 53                         | 3/4                 | 120                   | 0.59                     | \$309                           |
|                  |                  | 40           | 22V40F1     | 38       | 32  | 38.4 | 32.3                    | 73                                | 61-3/4                                   | 58-3/8           | 18-1/8     | 14-1/2                      | 3                 | 8                            | 52-1/4                     | 3/4                 | 120                   | 0.59                     | \$309                           |
|                  |                  | 38           | 42V40F      | 40       | 34  | 40.4 | 34.3                    | 68                                | 61-1/2                                   | 57-3/4           | 19-3/4     | 14-1/2                      | 3                 | 8                            | 52-1/4                     | 3/4                 | 125                   | 0.60                     | \$304                           |
|                  |                  | 50           | 22V50F1     | 38       | 36  | 38.4 | 36.4                    | 90                                | 61-1/2                                   | 58-1/4           | 20-1/8     | 14-1/2                      | 3                 | 8                            | 51-3/8                     | 3/4                 | 130                   | 0.58                     | \$315                           |
|                  |                  | 50           | 42V50-40F   | 40       | 36  | 40.4 | 36.4                    | 82                                | 61-1/2                                   | 58               | 21-3/4     | 14-1/2                      | 3                 | 8                            | 52-1/2                     | 3/4                 | 150                   | 0.58                     | \$315                           |
|                  |                  | 50           | 42V50-50F   | 50       | -   | 50.5 | -                       | 81                                | 62                                       | 58               | 21-3/4     | 14-1/2                      | 4                 | 8                            | 52-1/2                     | 3/4                 | 150                   | 0.58                     | \$315                           |
|                  | SHORT            | 30           | 22V30S-30F  | 30       | -   | 30.3 | -                       | 50                                | 49-3/4                                   | 46-1/4           | 19-3/4     | 14-1/2                      | 3                 | 8                            | 40-1/4                     | 3/4                 | 98                    | 0.61                     | \$299                           |
|                  |                  | 40           | 42VR40S-40F | 40       | 36  | 40.4 | 36.4                    | 72                                | 53-7/8                                   | 50-1/2           | 23         | 14-1/2                      | 3                 | 8                            | 44                         | 3/4                 | 135                   | 0.62                     | \$294                           |
|                  |                  | 40           | 22V40SF     | 36       | 34  | 36.4 | 34.3                    | 72                                | 52-3/4                                   | 49-3/8           | 20-1/8     | 14-1/2                      | 3                 | 8                            | 42-3/4                     | 3/4                 | 130                   | 0.59                     | \$309                           |
|                  |                  | 40           | 42V40SF     | 40       | 36  | 40.4 | 36.4                    | 72                                | 53-7/8                                   | 50-1/2           | 20-1/8     | 14-1/2                      | 3                 | 8                            | 44                         | 3/4                 | 130                   | 0.59                     | \$309                           |
|                  |                  | 50           | 42V50SF     | 40       | 36  | 40.4 | 36.4                    | 84                                | 54-1/4                                   | 49-3/4           | 22-1/4     | 14-1/2                      | 3                 | 8                            | 44                         | 3/4                 | 158                   | 0.59                     | \$309                           |

SPECIFY LP GAS WHEN ORDERING. Add "P" suffix to the model number. Example: 42VR40-40PF. • 40 ng/J NOx Compliant

## **Rheem Guardian System Features...**



## Exclusive Combustion Shut-off System

Should a spill incident occur, the Guardian System shuts off the gas supply and the air supply preventing a sustained vapor burn in the combustion chamber.


These units are designed to meet or exceed ANSI (American National Standards Institute) requirements and

energy efficiency performance criteria for energy

have been tested according to D.O.E. test procedures and meet or exceed the energy efficiency requirements of

NAECA, ASHRAE standard 90, ICC Code and all state

Before purchasing this appliance, read important energy cost and efficiency information available from your supplier.




Flame Arrestor Plate A specially-designed flame arrestor prevents ignition of vapors outside the combustion chamber.



Maintenance Free Superior air filtration prevents the flame arrestor from becoming clogged by lint, dust and oil.





In keeping with its policy of continuous progress and product improvement, Rheem reserves the right to make changes without notice.

Rheem Water Heating • 101 Bell Road, Montgomery, Alabama 36117-4305 • www.rheem.com

consuming appliances.