


PART NUMBER
E1937
JJ-MRKING



No.	DESCRIPTION	MATERIAL
1	STEM	CAST LOW LEAD BRASS ALLOY
2	O-RING	EPDM ASTM D2000
3	BALL	CAST LOW LEAD BRASS ALLOY
4	GASKET - SEAL	NITRILE ASTM D2000
5	BODY	CAST LOW LEAD BRASS ALLOY
6	O-RING	EPDM ASTM D2000
7	END PIECE	CAST LOW LEAD BRASS ALLOY
8	PJ GASKET	BUNA-N ASTM D2000
9	PJ WASHER	POLYPROPYLENE
10	CLPG NUT SUB	CAST BRASS ASTM B62 ALLOY C83600

VALVE SIZE	A
3/4"	3-5/8"
1"	4-41/64"
1-1/2"	5-5/32"
1-1/2x2"	5-1/8"
2"	7-5/16"

FILEPATH: PROD-ENG\JJ\SUBMITTALS\E1937

						DRFTR	RWB	6/9/08	JAMES JONES CO.	
						CHKR				
						ENGR				
						MGR				
							BY	DATE	UNLESS OTHERWISE NOTED SURFACE PREPARATION: BREAK CORNER(S) ---- .000 SURFACE FINISH -- XX RMS TOLERANCE(S): LINEAR ----- ± .000 ANGULAR ----- ± 0°00'	
						STK No				
						MAT'L				
						DESCR.	BALL TYPE CORPORATION VALVE (AWWA TAPER x PJ CTS)			
REV	ECR	DESCRIPTION	DATE	BY	CHKR				THIRD ANGLE PROJECTION  REF. No. SCALE	
									PART NUMBER E1937	