

NEWPORT KITCHEN

Features


Reverse Osmosis Cold Water Dispenser Faucet

- Solid brass construction
- Spring-loaded, normally closed toggle-style valve and handle
- Spout assembly with integral supply nipple
- 6-1/8" (15.6 cm) spout height at outlet
- 3-1/8" (7.9 cm) spout reach (c-c)
- 1.5 gallons (5.7 liters) per minute maximum flow rate
- For single hole configurations



Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- NSF 61
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations



Colors / Finishes

10B: Oil Rubbed Bronze15: Polished Nickel

15S: Satin Nickel26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.

Specified Model Model Description Colors / Finishes 104B Reverse Osmosis Cold Water Dispenser Faucet 15 15S 26 10B Other

Product Specification: Add "Color / Finish" suffix to Model number, below.

The Reverse Osmosis Cold Water Dispenser Faucet shall be made of solid brass construction. Faucet shall incorporate a spout assembly with integral supply nipple and feature a spring-loaded, normally closed toggle-style valve and handle. Faucet shall incorporate an integral air gap to meet the functional requirements of a reverse osmosis system (not included). Reverse Osmosis Cold Water Dispenser Faucet shall have a 1.5 gallons (5.7 liters) per minute maximum flow rate and accommodate single hole configurations. Product shall incorporate a 6-1/8" (15.6 cm) spout height at outlet and a 3-1/8" (7.9 cm) spout reach (c-c). Reverse Osmosis Cold Water Dispenser Faucet shall be Newport Brass Model 104B/____.

Product Dimensions (units are in inches)

