S









Stainless

Lock mode

1175BEV

1000 SERIES

FEATURES

PERFORMANCE

- 5.6 cubic feet overall storage capacity allows for up to 16 (.75L) wine bottles, 48 - 12 oz beer bottles and 65 - 12 oz. cans
- Touch pad digital control
- Double-zone cooling system provides a stable and consistent environment for optimum beverage storage
- Temperature setting from 34 to 45° F
- Sabbath / Blackout mode turns off all lighting, controls display and automatically resets after 36 hours
- UL residential and commercial listings




Double Zone Sytem featured in 1175BEV.

- Lighted black interior optimizes elegant display and easy viewing of contents and can be manually turned on for display of contents with door closed; automatically shuts off after four hours
- Two solid beech wood trimmed, 3/4 extension black powder coated wine racks
- Two tempered glass shelves with bullnose edge to maximize storage potential
- Standard commercial stainless steel handle is interchangeable with professional handle option
- Stainless steel model has stainless wrap with black caps on top and bottom to make this unit field reversible
- LowE coated, argon gas filled thermopane glass door provides protection from potentially harmful UV rays and added insulating energy efficiency
- · Black vinyl clad textured cabinet is more resistant to scratching, peeling and flaking
- Optional locking door model must be ordered right-hand or left-hand hinge specific

INTERIOR / EXTERIOR

- Solid beech wood trim on wine racks can be stained to match surrounding cabinetry
- Unit can be built-in or freestanding providing a custom aesthetic
- Allow a 2-1/2" clearance on hinged side for 90° door opening when installed adjacent
- Allow 1/4" width overall for proper installation (see backside for details)
- No additional clearance around sides, top or rear of unit is needed for ventilation
- Durable, factory installed level legs provide a more precise undercounter fit
- · Do not obstruct front grille air flow

^{*}Lock model must be ordered right-hinge or left-hinge specific.



1175BEVS Stainless Model

DIMENSIONS AND SPECIFICATIONS

OVERALL DIMENSIONS

34-1/8" (86.6) Height Width 23-15/16" (60.8) 23-5/16" (59.2) Depth 25-3/16" (63.9) With stainless steel handle

1175BEV	
Stainless	U-1175BEVS-00
Stainless, RH with lock	U-1175BEVS-13
Stainless, LH with lock	U-1175BEVS-15

Shipping weight:


Stainless steel wrap 126 lbs (58 kg)

Running amps 2.4 Maximum start-up amps 9.8

110/115 volt, 60 Hz Amps pertain to voltage rating

Capacities:

Automatic Defrost technology 5.6 Cu. Ft Refrigerator volume Wine bottle storage (0.75L) Up to 16 Up to 48 I2oz bottles Shelf storage and 65 12 oz cans



Please visit www.u-line.com for installation guide.

All specifications are subject to change without notice.

