

## **CONTROLS**








Fig. 1 Fig. 2 Fig. 3

CONTROLS			
PROSELECT PN	OLD PROSELECT PN	ADDITIONAL FEATURES	PIC FOR FIGURE
PSW12201	PS9002518	Hot Surface Ignition	Fig. 1
PSW12202	PS9006143	Fits all FVIR gas water heaters	Fig. 2
PSW12203	PS9003496	Fits all C3 design natural gas water heaters	
PSW12204	PS9003521	FV Pilot Assembly 200° - NATURAL GAS ONLY / C3 applications	Fig. 3
PSW12205	PS9003542	FV Pilot Assembly 190° - NATURAL GAS ONLY, high altitude / C3 applications	
PSW12206	PS9003563	Fits 40 gallon C3 design State & A.O.Smith natural gas water heater	
PSW12207	PS9003626	Hot surface igniter	
PSW12208	PS9003638	Natural gas control valve for residential, 40,000 BTU input	
PSW12210	PS9004519	Hot surface igniter for BTH,SUF 970 series commercial gas water heaters	
PSW12211	PS9004541	Natural pilot burner for BTC-120 thru 500A series 970 and up.	
PSW12212	PS9004544	Honeywell® I.I.D control, Intermittent Ignition control - natural & propane for BTC 120 thru 500A, series 970 & up	
PSW12213	PS9004570	Control thermostat	
PSW12214	PS9004586	Switch-fan prover	
PSW12215	PS9005256	Commercial hot surface igniter	
PSW12216	PS9005886	For BTH, SUF high efficiency gas models	
PSW12217	PS9005900	For BTH, SUF high efficiency gas models	
PSW12218	PS9006101	Igniter (natural & propane)	
PSW12703	PS9000249	NATURAL GAS -long shank-2 5/8" shank	
PSW12708	PS9001954	W/E.C.O. 12/240 V.A.C.	
PSW12709	PS9002123	PROPANE GAS-long shank, left hand threads, for models manufactured 6-1-93 or after	
PSW12710	PS9002353	Gas valve-PROPANE-40 & 50 galshort shank	

## **Warranty and Codes**

These PROSELECT products carry a 1-year limited warranty except where noted.