

Type _____

-84


P4421 ☐

P4422 ☐

Finish

Dimensions (Inches)

Catalog No.	Espresso	Lamping	A	B	C
P4421	-84	4 (m) 100w	28-3/8	21-3/8	96
P4422	-84	5 (m) 100w	32	26-1/8	101



Specifications:

General

- Arched arms terminated with cream linen fabric drum shades: 7-1/8" dia. x 5-1/2" ht.
- Adjustable turnkey on each arm for customized shade direction
- Multi rod center column
- Six feet of 9 gauge chain supplied
- Painted Espresso (-84) finish
- Steel Construction
- Companion chandeliers, pendants, close to ceiling, and wall bracket fixtures available

Mounting

- Ceiling mounted on chain
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- Medium based ceramic sockets
- 15 feet of wire supplied
- Pre-wired

Labeling

- UL-CUL listed