


Split System Cooling Product Data

XR 13 4TTR3018-060

 $1\frac{1}{2} - 5$ Tons





Features and Benefits

- Climatuff® compressor
- Efficiency up to 14.00 SEER
- All aluminum **Spine Fin™** coil
- WeatherGuard™ fasteners
- Quick-Sess[™] cabinet, easy service access and refrigerant connections with full coil protection
- **DuraTuff™** base, fast complete drain, weather proof
- Comfort "R"™ mode approved
- · Glossy corrosion resistant finish
- Internal high/low pressure and temperature protection
- 018, 024, 030, 036 ship with start kit
- Liquid line filter-drier

- Tarpaulin gray cabinet with anthracite gray badge & cap
- High pressure switch
- R-410A refrigerant
- S.E.E.T. design testing
- 100% line run test
- Low ambient cooling to 55°F as shipped
- Low ambient cooling to 30°F with AY28X079
- Low ambient cooling to 0°F with BAYLOAM103
- Extended warranties available



Contents

Features and Benefits	2
General Data	4
Product Specifications	4
A-weighted Sound Power Level [dB(A)]	4
Accessory Description and Usage	5
AHRI Standard Capacity Rating Conditions	5
Model Nomenclature	6
Electrical Data	7
Dimensions	10
Mechanical Specification Options	11

22-1842-07 3



General Data

Product Specifications

Model No. 1	4TTR3018E1	4TTR3024E1	4TTR3030E1	4TTR3036D1
Electrical Data V/Ph/Hz ②	208/230/1/60	200/230/1/60	208/230/1/60	208/230/1/60
Min Branch Cir Ampacity	9	12	15	18
Br. Cir. Prot. Rtg Max (Amps)	15	20	25	30
Compressor	CLIMATUFF®	CLIMATUFF®	CLIMATUFF®	CLIMATUFF®
RL Amps - LR Amps	6.4 - 40	8.9 - 48.5	11.5 - 63.5	14.0 - 63
Outdoor Fan FL Amps	0.74	0.74	0.74	0.74
Fan HP	1/8	1/8	1/8	1/8
Fan Dia (inches)	23.0	23.0	23.0	23.0
Coil	Spine Fin™	Spine Fin™	Spine Fin™	Spine Fin™
Refrigerant R-410A	4/15-LB/OZ	5/8-LB/OZ	5/2-LB/OZ	6/9-LB/OZ
Line Size - (in.) O.D. Gas 3	5/8	5/8	3/4	3/4
Line Size - (in.) O.D. Liquid ③	3/8	3/8	3/8	3/8
Charge Spec. Subcooling	8°	10°	10°	10°
Dimensions H x W x D (Crated)	34 x 30.1 x 33	34 x 30.1 x 33	34 x 30.1 x 33	38 x 30.1 x 33
Weight - Shipping	191	196	200	217
Weight - Net	165	169	173	190
Start Components	YES	YES	YES	YES
Sound Enclosure	YES	NO	NO	NO
Compressor Sump Heat	NO	NO	NO	NO
Optional Accessories: 4				
Anti-short Cycle Timer	TAYASCT501A	TAYASCT501A	TAYASCT501A	TAYASCT501A
Evaporator Defrost Control	AY28X079	AY28X079	AY28X079	AY28X079
Rubber Isolator Kit	BAYISLT101	BAYISLT101	BAYISLT101	BAYISLT101
Extreme Condition Mounting Kit	BAYECMT023	BAYECMT023	BAYECMT023	BAYECMT023
Start Kit				
Crankcase Heater Kit	BAYCCHT300	BAYCCHT300	BAYCCHT300	BAYCCHT300
Seacoast Kit	BAYSEAC001	BAYSEAC001	BAYSEAC001	BAYSEAC001
Low Ambient Kit	BAYLOAM103	BAYLOAM103	BAYLOAM103	BAYLOAM103
Refrigerant Lineset 5	TAYREFLN950	TAYREFLN950	TAYREFLN7*	TAYREFLN7*

Certified in accordance with the Unitary Air-Conditioner equipment certification program which is based on AHRI Standard 210/240.
 Calculated in accordance with N.E.C. Only use HACR circuit breakers or fuses.
 Standard line lengths - 60'. Standard lift - 60' Suction and Liquid line.

MODEL	SOUND POWER LEVEL [dB(A)]		A-WFIC	HTED FUL	L OCTAVE S	OUND POWE	BIEVEL dB	[(dB(A)]	
	[63	125	250	500	1000	2000	4000	5000
4TTR3018E1	76	77	71	67	73	67	72	62	55
4TTR3024E1	75	79	70	66	69	70	70	62	55
4TTR3030E1	76	77	68	69	70	69	72	61	58
4TTR3036D1	75	78	74	67	72	72	66	62	57
4TTR3042D1	74	76	73	69	71	70	64	58	53
4TTR3048D1	75	80	73	70	72	71	65	63	59
4TTR3060D1	75	80	73	70	72	71	65	63	59
Note: Rated in accordance with AHRI Standard 270-2008									

For Greater lengths and lifts refer to refrigerant piping software Pub# 32-3312-0[†]. (†denotes latest revision)

For accessory description and usage, see page 5.
 * = 15, 20, 25, 30, 40 and 50 foot lineset available.



General Data

Product Specifications

Model No. 1	4TTR3042D1	4TTR3048D1	4TTR3060D1
Electrical Data V/Ph/Hz ②	208/230/1/60	208/230/1/60	208/230/1/60
Min Cir Ampacity	26	28	35
Max Fuse Size (Amps)	45	50	60
Compressor	CLIMATUFF® - SCROLL	CLIMATUFF® - SCROLL	CLIMATUFF® - SCROLL
RL Amps - LR Amps	19.9 - 105	21.8 - 117	26.8 - 134
Outdoor Fan FL Amps	0.93	0.93	0.93
Fan HP	1/5	1/5	1/5
Fan Dia (inches)	27.5	27.5	27.5
Coil	Spine Fin™	Spine Fin™	Spine Fin™
Refrigerant R-410A	6/2-LB/OZ	6/13-LB/OZ	8/0-LB/OZ
Line Size - (in.) O.D. Gas 3	3/4	7/8	7/8
Line Size - (in.) O.D. Liquid 3	3/8	3/8	3/8
Charge Spec. Subcooling	10°	10°	10°
Dimensions H x W x D (Crated)	34.4 x 35.1 x 38.7	34.4 x 35.1 x 38.7	42.4 x 35.1 x 38.7
Weight - Shipping	228	235	261
Weight - Net	196	203	226
Start Components	NO	NO	NO
Sound Enclosure	NO	NO	NO
Compressor Sump Heat	NO	NO	NO
Optional Accessories: 4			
Anti-short Cycle Timer	TAYASCT501A	TAYASCT501A	TAYASCT501A
Evaporator Defrost Control	AY28X079	AY28X079	AY28X079
Rubber Isolator Kit	BAYISLT101	BAYISLT101	BAYISLT101
Extreme Condition Mounting Kit	BAYECMT004	BAYECMT004	BAYECMT004
Start Kit	BAYKSKT263	BAYKSKT263	
Crankcase Heater Kit	BAYCCHT301	BAYCCHT301	BAYCCHT301
Seacoast Kit	BAYSEAC001	BAYSEAC001	BAYSEAC001
Low Ambient Kit	BAYLOAM103	BAYLOAM103	BAYLOAM103
Refrigerant Lineset 5	TAYREFLN7*	TAYREFLN3*	TAYREFLN3*

Accessory Description and Usage

Anti-Short Cycle Timer — Solid state timing device that prevents compressor recycling until five (5) minutes have elapsed after satisfying call or power interruptions. Use in area with questionable power delivery, commercial applications, long lineset, etc.

Evaporator Defrost Control — SPST Temperature actuated switch that cycles the condenser off as indoor coil reaches freeze-up conditions. Used for low ambient cooling to 30°F with TXV.

Rubber Isolators — Five (5) large rubber donuts to isolate condensing unit from transmitting energy into mounting frame or pad. Use on any application where sound transmission needs to be minimized.

Hard Start kit — Start capacitor and relay to assist compressor motor startup. Use in areas with marginal power supply, on long linesets, low ambient conditions, etc.

Extreme Condition Mount Kit — Bracket kits to securely mount condensing unit to a frame or pad without removing any panels. Use in areas with high winds, or on commercial roof tops, etc.

AHRI Standard Capacity Rating Conditions

AHRI STANDARD 210/240 RATING CONDITIONS —

- (A) Cooling 80°F DB, 67°F WB air entering indoor coil, 95°F DB air entering outdoor coil.
- (B) High Temperature Heating 47°F DB, 43°F WB air entering outdoor coil, 70°F DB air entering indoor coil.
- (C) Low Temperature Heating 17°F DB, 15°F WB air entering outdoor coil, 70°F DB air entering indoor coil.
- (D) Rated indoor airflow for heating is the same as for cooling.

AHRI STANDARD 270 RATING CONDITIONS — (Noise rating numbers are determined with the unit in cooling operation.) Standard Noise Rating number is at 95°F outdoor air.







22-1842-07 5





Model Nomenclature

6












Electrical Data

SCHEMATIC DIAGRAMS

(SEE LEGEND)

4TTR3018E1,024E1,030E1, and 036D1



- NOTES:
 I. IF OOT-B IS NOT USED. ADD JUMPER BETWEEN W2 & W3
 AT AIR HANDLER. IF USED, ODT-B MUST BE MOUNTED REMOTE OF CONTROL BOX IN AN APPROVED WEATHER PROOF ENCLOSURE.
 2. IF ODT-A IS NOT USED. ADD JUMPER BETWEEN WI & W2 AT AIR HANDLER.
- 3. LOW VOLTAGE (24 V) FIELD WIRING MUST BE IS AND MIN.

∆WARNING

HAZARDOUS VOLTAGE! DISCONNECT ALL ELECTRICAL POWER INCLUDING REMOTE DISCONNECTS BEFORE SERVICING. Failure to disconnect power before servicing can cause severe personal injury or death.

FOR CANADIAN INSTALLATIONS POUR INSTALLATIONS CANADIENNES


CAUTION: NOT SUITABLE FOR USE ON SYSTEMS EXCEEDING 150V-TO-GROUND ATTENTION: NE CONVIENT PAS AUX INSTALLATIONS DE PLUS DE 150 V A LA TERRE


∆CAUTION

USE COPPER CONDUCTORS ONLY! UNIT TERMINALS ARE NOT DESIGNED TO ACCEPT OTHER TYPES OF CONDUCTORS. Failure to do so may cause damage to the equipment.

PRINTED FROM D157097P01

4TTR3042D1





NOTES:

1. IF OFT-B IS NOT USED, ADD JUMPER BETHEEN BY E & BS AT AIR HANGLER, IF USED, COT-B HISTS BE NOWITCH OF CONTROL BOX IN AN APPROVED BETHEEN PROPO FENCIOSED.

2. IF OFT-A IS NOT USED, ADD JUMPER BETHEEN BIL BY A BS AN AIR AND AIR BETHEEN BIL BY A BY AIR HANGLER,

3. LOW YOUTAGE (24 V) FRIELD BIRING MUST BE IS AND MIN.

∆LWARN I NG

INCANDUOS VOLINGE!

DISCONNECT ALL ELECTRICAL POWER
INCLUDING REMOTE DISCONNECTS
BEFORE SERVICING.
Failure to disconnect power
before servicing can cause severe
ersonal injury or death.

FOR CANADIAN INSTALLATIONS POUR INSTALLATIONS CANADIENNES

CAUTION: NOT SUITABLE FOR USE ON SYSTEMS EXCEEDING 150V-TO-GROUND ATTENTION: NE CONVIENT PAS AUX INSTALLATIONS DE PLUS DE 150 Y A LA TERRE

∆CAUTION

USE COPPER CONDUCTORS ONLY!
UNIT TERMINALS ARE NOT DESIGNED
TO ACCEPT OTHER TYPES OF CONDUCTORS. Failure to do so may cause damage to the equipment.

PRINTED FROM D157047P01




Electrical Data


SCHEMATIC DIAGRAMS

(SEE LEGEND)

4TTR3048, 060D1

TO POWER SUPPLY PER UNIT NAMEPLATE AND LOCAL CODES





NOTES:

1. IF ODT-B IS NOT USED. ADD JUMPER BETWEEN
W2 & W3 AT AIR HANDLER. IF USED, ODT-B
MUST BE MOUNTED REMOTE OF CONTROL BOX IN MUST DE MOUNTED REMOTE OF CONTINUE DO A IN AM APPROVED HEATHER PROOF ENCLOSURE. 2. IF OOT-A IS NOT USED. ADD JUMPER BETWEEN WII & W2 AT AIR HANDLER. 3. LOW VOLTAGE (24 V) FIELD WIRING MUST DE 18 AWG MIN.

FOR CANADIAN INSTALLATIONS POUR INSTALLATIONS CANADIENNES

CAUTION: NOT SUITABLE FOR USE ON SYSTEMS EXCEEDING 150V-TO-GROUND ATTENTION: NE CONVIENT PAS AUX INSTALLATIONS DE PLUS DE 150 V A LA TERRE

∆NARNING

HAZARDOUS VOLTAGE! HAZARDOUS VOLIAGE!
DISCONNECT ALL ELECTRICAL POWER
INCLUDING REMOTE DISCONNECTS
BEFORE SERVICING.
Failure to disconnect power
before servicing con cause severe
personal injury or death.

∆CAUTION

USE COPPER CONDUCTORS ONLY!
UNIT TERMINALS ARE NOT DESIGNED
TO ACCEPT OTHER TYPES OF CONDUCTORS. Failure to do so may cause damage to the equipment.



Electrical Data

SCHEMATIC DIAGRAMS

LEGEND

COLOR OF WIRE

BK/BL BLACK WIRE WITH BLUE MARKER

COLOR OF MARKER

BK BLACK OR ORANGE YL YELLOW

BL BLUE RD RED GR GREEN

BR BROWN WH WHITE PR PURPLE

SYMBOLS

FACTORY WIRING LINE V. - - - 24 V. - - LINE V. FIELD WIRING — X — FIELD INSTALLED FACTORY WIRING GROUND JUNCTION 0 WIRE NUT OR CONNECTOR COIL \rightarrow \vdash CAPACITOR \dashv \vdash RELAY CONTACT (N.O.) 1 RELAY CONTACT (N.C.) **^** THERMISTOR INTERNAL OVERLOAD PROTECTOR PRESSURE ACTUATED SWITCH TEMP. ACTUATED SWITCH POL. PLUG FEMALE HOUSING (MALE TERM.) POL. PLUG MALE HOUSING (FEMALE TERM.) √✓✓ RESISTOR OR HEATING ELEMENT OMOTOR WINDING TERMINAL \circ

LPCO LOW PRESSURE CUTOUT SW COOLING ANTICIPATOR COOLING ANTICIPATOR
COIL BOTTOM SENSOR
FAN CAPACITOR
WIRE CONNECTOR
COMPRESSOR
RUN CAPACITOR
STARTING CAPACITOR
CAPACITOR SWITCHING RELAY
DEFROST CONTROL
INDOOR FAN RELAY
HEATING ANTICIPATOR LOW PRESSURE CUTOUT SW.
COMPRESSOR MOTOR CONTACTOR
OUTDOOR ANTICIPATOR
OUTDOOR FAN THERMOSTAT
OUTDOOR TEMPERATURE SENSOR
OUTDOOR THERMOSTAT
RESISTANCE HEAT SWITCH
SWITCHOVER VALVE SOLENOID
SYSTEM "ON-OFF" SWITCH CPR ODS CR CS ODT RHS SC DFC DISCHARGE LINE THERMOSTAT TRANSFORMER HA HEATING ANTICIPATOR HPCO HIGH PRESSURE CUTOUT SW. TNS HEATING-COOLING THERMOSTAT TS IOL INTERNAL OVERLOAD PROTECTOR TSH HEATING THERMOSTAT


9




Dimensions

4TTR3 OUTLINE DRAWING

NOTE: ALL DIMENSIONS ARE IN MM (INCHES)



TOP DISCHARGE AREA SHOULD BE UNRESTRICTED FOR AT LEAST 1524 (5 FEET) ABOVE UNIT. UNIT SHOULD BE PLACED SO ROOF RUN-OFF WATER DOES NOT POUR DIRECTLY ON UNIT, AND SHOULD BE AT LEAST 305 (12") FROM WALL AND ALL SURROUNDING SHRUBBERY ON TWO SIDES. OTHER TWO SIDES UNRESTRICTED.



MODELS BASE FIG. С В D Ε G н Κ 4TTR3018E1 1 730 (28-3/4) 829 (32-5/8) 756 (29-3/4) 3/8 143 (5-5/8) 92 (3-5/8) 210 (8-1/4) 79 (3-1/8) 508 (20) 4TTR3024E1 3 1 730 (28-3/4) 829 (32-5/8) 756 (29-3/4) 3/8 143 (5-5/8) 92 (3-5/8) 210 (8-1/4) 79 (3-1/8) 508 (20) 5/8 4TTR3030E1 3 1 730 (28-3/4) 829 (32-5/8) 756 (29-3/4) 143 (5-5/8) 92 (3-5/8) 210 (8-1/4) 79 (3-1/8) 508 (20) 4TTR3036D1 3 1 832 (32-3/4) 829 (32-5/8) 756 (29-3/4) 3/4 3/8 143 (5-5/8) 92 (3-5/8) 210 (8-1/4) 79 (3-1/8) 508 (20) 4TTR3042D1 4 741 (29-1/8) 946 (37-1/4) 870 (34-1/4) 3/4 3/8 152 (6) 98 (3-7/8) 219 (8-5/8) 86 (3-3/8) 508 (20) 4TTR3048D1 1 4 741 (29-1/8) 946 (37-1/4) 870 (34-1/4) 7/8 3/8 152 (6) 98 (3-7/8) 219 (8-5/8) 86 (3-3/8) 508 (20) 4TTR3060D1 4 1 943 (37-1/8) 946 (37-1/4) 870 (34-1/4) 7/8 3/8 98 (3-7/8) 219 (8-5/8) 86 (3-3/8) 152 (6) 508 (20)

From Dwg. D152898



Mechanical Specification Options

General

The 4TTR3-D models shall be fully charged from the factory for matched indoor section and up to 15 feet of piping. This unit must be designed to operate at outdoor ambient temperatures as high as 115°F. Cooling capacities shall be matched with a wide selection of air handlers and furnace coils that are AHRI certified. The unit is certified to UL 1995. Exterior must be designed for outdoor application.

Casing

Unit casing is constructed of heavy gauge, galvanized steel and painted with a weather-resistant powder paint. Corrosion and weatherproof CMBP-G30 DuraTuffTM base.

Refrigerant Controls

Refrigeration system controls include condenser fan and compressor contactor. High and low pressure controls are inherent to the compressor. Another standard feature is the liquid line dryer.

Compressor

The Climatuff® compressor features internal over temperature and pressure protector, total dipped hermetic motor and thermostatically controlled sump heater. Other features include: Centrifugal oil pump, and low vibration and noise.

Condenser Coil

The Spine Fin™ coil shall be continuously wrapped, corrosion resistant all aluminum with minimum brazed joints. This coil is 3/8 inch O.D. seamless aluminum glued to a continuous aluminum fin. Coils are lab tested to withstand 2,000 pounds of pressure per square inch. The outdoor coil provides low airflow resistance and efficient heat transfer. The coil is protected on all four sides by louvered panels.

Low Ambient Cooling

As manufactured, this unit has a cooling capability to 55°F. The addition of an evaporator defrost control permits operation to 30°F. The addition of a low ambient kit with TXV permits low ambient cooling to 0°F.

Accessories

Thermostats — Heating/Cooling (manual and automatic changeover). Sub-base to match thermostat and locking thermostat cover.

Evaporator Defrost Control — See Low Ambient Cooling.

Outdoor Thermostat — Supplemental heat outdoor ambient lockout from 46 to -10° F.

22-1842-07 11







	04/12