

# Check Valves

## UL, ULC and FM



### Description

Check valves feature cast brass\* bodies with a spring loaded clapper assembly making this valve suitable for vertical or horizontal installations. Features metal faced clapper with O-ring seat. Rated to 300 psi. Valve bodies are tapped and plugged 1/2" IPS for additional equipment such as a ball drip valve when used in conjunction with a Fire Department Connection or a pressure gauge when used in a supply line.

### Installation

Install in accordance with approved installation practices. Use an approved thread sealant such as PipeFit Thread Sealing Paste with PTFE on all threaded connections. Make sure that proper lubrication has been applied to groove coupling gaskets for groove end valves.

**DO NOT OVER TIGHTEN  
THREADED CONNEC-  
TIONS. OVERTIGHTEN-  
ING MAY CAUSE DISTOR-  
TION OF THE BODY AND  
THREADS OF THE VALVE  
LEADING TO IMPPROPER  
PERFORMANCE AND  
PRODUCT FAILURE.**

### Specifications

**Material:**

Cast Brass\*

**Pressure Rated:**

300psi

**Size:**

2" IPS  
2 1/2" IPS  
3" IPS  
4" IPS

**Configurations:**

(Inlet x Outlet)  
MNPT x FNPT  
MNPT x GRV  
GRV x GRV

\*Contains lead. Not for use in water systems intended for human consumption.

