



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
6.00"	22.50"	4.00"
<u>BP Height</u>	<u>BP Width</u>	
4.75"	4.75"	
<u>Hanging Weight</u>		
5.27 lb		

Lamping:

Xenon G9 Frost	2,400 Rated Lumens
3.00 50W G9 Frost	2900 Color Temperature
150 total watt	2,000 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
7.50 lb	7.63"	7.38"	28.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209900301	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Dusty White DW

Material:

Steel

Certification:

Damp Location
ADA

Additional:

G9 Frost (Included)
Lighting Direction: