

## Combi2® TTW®

### Residential Power Vent Combi2® TTW® Gas Water Heater System



Photo is of  
**C-DW2-TW50T10FBN**

#### FEATURING:



#### The Combi2® TTW® FVIR Defender Safety System® Models Feature (50T model, only):

- **Advanced ScreenLok® Technology Flame Arrestor Design**—Flame arrestor is designed to prevent ignition of flammable vapor outside of the water heater.
- **Flammable Vapor Sensor**—Electronic sensor prevents burner operation if flammable vapors are detected. The sensor will also prevent operation if there is ongoing flammable vapors burning inside the combustion chamber.
- **Maintenance Free**—Regular cleaning of air inlet openings or flame arrestor is not required under normal conditions.
- **Sight Window**—Offers a view of the pilot and burner operation.

#### All Combi2® TTW® Models Feature

- **Powerful Blower Motor**—Exclusively featuring the AquaVENT MAX™ from Fasco™ is the quietest blower motor in the industry. This new blower is a lower profile than previous versions and features a more robust electrical connection
  - 10 Foot (3m) Power Cord—Included (120 VAC)
- **Horizontal and Vertical Venting**—With 3" (76mm) or 4" (102mm) PVC, ABS or CPVC (Maximum equivalent vent lengths on reverse side).
- **High Altitude Ready**—Water Heaters designed and certified for installations up to 10,100 feet (3078m) out of the box. No conversion kit required.
- **Internal Double Wall Heat Exchanger**—1½" (38mm) O.D. glass coated (Vitrageglas® with Microban®) steel coil ensures separation of potable water and heating fluid.
  - ¾" (19mm) NPT Solar Collector Supply and Return Connections.
- **Low Heat Exchanger Head Loss**—Up to 8 GPM flow, with less than 6 ft. of head loss. Greatly reduces the required pump size for heat exchange.
- **Bradford White ICON System®**—Intelligent gas control with spark to pilot ignition system that eliminates the constant burning pilot. This results in savings of pilot gas during stand-by periods (120 VAC).
  - **Enhanced Performance**—Proprietary algorithms provide enhanced First Hour Rating and tighter temperature differential.
  - **Advanced Temperature Control System**—Microprocessor constantly monitors and controls burner operation to maintain accurate water temperature levels.
  - **Intelligent Diagnostics**—An exclusive green LED light prompts the installer during start-up and provides ten different diagnostic codes to assist in troubleshooting.
- **Vitrageglas® Lining with Microban®**—An exclusively engineered enamel formula that provides superior tank protection from the corrosive effects of water; and with Microban® antimicrobial product protection to help prevent the growth of bacteria, mold and mildew on the surface of the tank lining.
- **Factory-Installed Hydrojet® Total Performance System**—Sediment reducing device that also increases first hour rating of hot water while minimizing temperature build-up in tank.
- **Insulation System**—2" (51mm) Non-CFC foam insulation covers the sides and top of the tank, reducing heat loss. This results in less energy consumption, improved efficiencies, and jacket rigidity.
- **Pedestal Base.**
- **Water Connections**—¾" (19mm) NPT factory-installed true dielectric fittings extend water heater life and simplify water line connections.
- **Two Protective Anode Rods.**
- **T&P Relief Valve**—Installed.
- **Low Restrictive Brass Drain Valve**—Durable tamper proof design.
- **Thermostatic Mixing Valve (ASSE Approved)**—Included.

#### 10-Year Limited Tank and Heat Exchanger Warranties / 6-Year Limited Warranty on Component Parts.

For more information on warranty, please visit [www.bradfordwhite.com](http://www.bradfordwhite.com)

For products installed in USA, Canada, and Puerto Rico. Some states do not allow limitations on warranties. See complete copy of the warranty included with the heater.

Microban® antimicrobial product protection helps prevent the growth of bacteria, mold and mildew that may affect the product. The built-in antimicrobial properties do not protect users or others from disease-causing organisms. Microban® is a registered trademark of Microban Products Company.

MANUFACTURED UNDER ONE OR MORE OF THE FOLLOWING U.S. PATENTS: 5,682,666; 7,634,976; 5,660,165; 5,954,492; 6,056,542; 6,935,280; 5,372,185; 5,485,879; 5,574,822; 7,971,560; 7,992,526; 6,684,821; 7,334,419; 7,866,168; 7,270,087; 7,007,748; 5,596,952; 6,142,216; 7,699,026; 5,341,770; 7,337,517; 7,665,211; 7,665,210; 7,063,132; 7,063,133; 7,559,293; 7,900,589; 5,943,984; 8,082,888; 5,988,117; 7,621,238; 7,650,859; 5,761,379; 7,409,925; 5,277,171; 8,146,772; 7,458,341; 2,262,174. OTHER U.S. AND FOREIGN PATENT APPLICATIONS PENDING. CURRENT CANADIAN PATENTS: 2,314,845; 2,504,824; 2,108,186; 2,143,031; 2,409,271; 2,548,958; 2,112,515; 2,476,685; 2,239,007; 2,092,105; 2,107,012. Defender Safety System®, ScreenLok®, TTW®, Vitrageglas® and Hydrojet® are registered trademarks of Bradford White® Corporation. Microban® is a registered trademark of Microban Products Company.

# Residential Power Vent Combi2® TTW® Gas Water Heater System

## Combi2® TTW® Models "19 Series"

NATURAL GAS AND LIQUID PROPANE GAS

Meet or exceed ASHRAE 90.1 (latest edition). C.E.C. Listed  
80% Recovery Efficiency


Model Number	Rated Nominal Volume		Nat. BTU/Hr. Input	LP BTU/Hr. Input	Recovery 90°F Rise*				A Floor to Top of Blower	B Jacket Dia.	C Vent Size	D Floor to T&P Conn.	E Floor to Gas Conn. in.	F Floor to Exchanger Inlet	G Floor to Exchanger Outlet	H Floor to Heater Top in.	J Floor to Water Conn. in.	K Depth	Approx. Shipping Weight
	U.S. Gal.	Imp. Gal.			Nat. U.S. GPH	Nat. Imp. GPH	LP U.S. GPH	LP Imp. GPH											
C-DW2-TW50T10FBN	45	38	67,000	60,000	72	60	65	54	63 <sup>3</sup> / <sub>16</sub>	22	3 or 4	50%	11%	28	50%	56%	60%	26%	245
C-DW2-TW75T10BN	72	61	76,000	75,500	82	69	81	67	66 <sup>1</sup> / <sub>2</sub>	26	3 or 4	53	15	30%	53	60%	64%	31	315

Model Number	Rated Nominal Volume		Nat. kW Input	LP kW Input	Recovery 50°C Rise*		A Floor to Top of Blower	B Jacket Dia.	C Vent Size	D Floor to T&P Conn.	E Floor to Gas Conn. mm.	F Floor to Exchanger Inlet	G Floor to Exchanger Outlet	H Floor to Heater Top mm.	J Floor to Water Conn. mm.	K Depth	Approx. Shipping Weight
	Liters				Nat. Liters/Hour	LP Liters/Hour											
C-DW2-TW50T10FBN	170		19.6	17.5	272	246	1621	559	76 or 102	1273	298	711	1273	1432	1543	679	111
C-DW2-TW75T10BN	272		22.3	22.1	310	306	1684	660	76 or 102	1346	389	784	1549	1530	1632	787	143

Propane models feature a Titanium Stainless Steel propane burner. For Propane (LP) models change suffix "BN" to "SX".

\* Based on manufacturers rated recovery efficiency.

120 VAC Required for Power Venting / 120 VAC, 60Hz., 3.1 Amperes.



Heat Exchanger Head Loss		Heat Exchanger Head Loss	
GPM	Ft. of Hd. Loss	LPM	m of Hd. Loss
2	0.15	7.6	0.0457
5	0.94	18.9	0.2865
8	2.40	30.2	0.7315
10	3.75	37.9	1.1430
12	5.40	45.4	1.6459

C-DW2-TW50T10FBN C-DW2-TW75T10BN	3" (76mm) Vent Pipe	4" (102mm) Vent Pipe
Max. Equivalent Length	†75 ft. †23.0m	†180 ft. †55.0m
Min. Equivalent Length	7 ft. 2.1m	15 ft. 4.6m
Number of 90° Elbows	1 70 ft. 21.3m 2 65 ft. 20.0m 3 60 ft. 18.3	175 ft. 53.3m 170 ft. 52.0m 165 ft. 50.3m

Subtract 5 ft. (1.5m) for each additional 90° elbow.

† For high altitude installations, consult the installation instructions.

Heat Exchanger Values*					
Supply Temperature	140°F	60°C	120°F	49°C	100°F 38°C
Return Temperature	120°F	49°C	100°F	38°C	80°F 27°C
Differential	20°F	11°C	20°F	11°C	20°F 11°C
Flow Rate	2.3 GPM	8.7 LPM	3.4 GPM	12.9 LPM	4.4 GPM 16.7 LPM
Net Output	20,000 BTU/Hr.	5.9kW	29,000 BTU/Hr.	8.5kW	38,000 BTU/Hr. 11.1kW

\* These values were obtained using 180°F (82°C) stored tank temperature.

Net Output is the space heating capacity based on normal piping and pickup allowance of 15%.

Actual values may vary based on circulator flow rate, number of zones, water and space heating demands. Numbers subject to change.

### General

#### Meets NAECA Requirements.

All gas water heaters are certified at 300 PSI test pressure (2068 kPa) and 150 PSI working pressure (1034 kPa). All potable water and heat exchanger connections are 3/4" (19mm) NPT on 11" (279mm) centers. All gas connections 1/2" (13mm). All models design certified by CSA International (formerly AGA/CGA), ANSI Z21.10.1 and or 10.3 and peak performance rated.

**Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.**

#### Suitable for Water (Potable) Heating and Space Heating.

Toxic chemicals, such as those used for boiler treatment, shall NEVER be introduced into the potable water side. The potable side of this unit may NEVER be connected to any existing heating system or component(s) previously used with a non-potable water heating appliance. The heat exchanger side of the unit may be used in space heating applications.

— BRADFORD WHITE IS —

**AMERICAN  
STRONG**

Sales: 800-523-2931 ■ Fax 215-641-1612

24/7 Technical Support: 800-334-3393 ■ Email techserv@bradfordwhite.com

Products made by Bradford White are manufactured in the United States using the finest raw materials and components from around the world.

**Built to be the Best®**