

TTW4

Light Duty Commercial Power Vent Energy Saver Gas Water Heaters



Photo is of
TW4-65S-70FB-3N

FEATURING:

DEFENDER
SAFETY SYSTEM™



AHR



3 or 5-Year Limited Tank Warranties / 1-Year Limited Warranty on Component Parts.

For more information on warranty, please visit www.bradfordwhite.com

For products installed in USA, Canada and Puerto Rico. Some states do not allow limitations on warranties. See complete copy of the warranty included with the heater.

The TTW[®]4 FVIR Defender Safety System[®] Models Feature (50 and 65 gallon models, only):

- **Advanced ScreenLok[®] Technology Flame Arrestor Design**—Flame arrestor is designed to prevent ignition of flammable vapor outside of the water heater
- **Flammable Vapor Sensor**—Electronic sensor prevents burner operation if flammable vapors are detected. The sensor will also prevent operation if there is ongoing flammable vapor burn inside the combustion chamber.
- **Maintenance Free**—No regular cleaning of air inlet openings or flame arrestor is required under normal conditions.
- **Sight Window**—Offers a view into the combustion chamber to observe the operation of the pilot and burner.

All TTW[®]4 Models Feature:

- **Factory Installed Hydrojet[®] 2™ Total Performance System**—Cold water inlet sediment reducing device helps prevent sediment build up in tank. Increases first hour delivery of hot water while minimizing temperature build up at top of tank.
- **Vitraglas[®] Lining**—Bradford White tanks are lined with an exclusively engineered enamel formula that provides superior tank protection from the highly corrosive effects of hot water. This formula (Vitraglas[®]) is fused to the steel surface by firing at a temperature of over 1600° F.
- **Powerful Blower Motor**—Our significantly quiet design has greater resistance to outside winds and the power to vent in many difficult venting situations.
- **Honeywell Self Diagnostic Electronic Gas Control**—Intelligent gas control with spark to pilot ignition system eliminates the constant burning pilot. This results in savings of pilot gas during stand by periods (120 V.A.C.).
 - **Enhanced Performance**—Proprietary algorithms provide enhanced First Hour Delivery ratings and tighter temperature differentials.
 - **Advanced Temperature Control System**—Microprocessor constantly monitors and controls burner operation to maintain accurate and consistent water temperature levels (up to 180°F).
 - **Intelligent Diagnostics**—An exclusive green LED light prompts the installer during start-up and provides ten different diagnostic codes to assist in troubleshooting.
 - **Pilot On Indication**—Flashing green LED provides positive indication that pilot is on.
- **Horizontal and Vertical Venting**—With 3" or 4" PVC, ABS, or CPVC (Maximum equivalent vent length on reverse side).
- **2" Non-CFC Foam Insulation**—Covers the sides and top of tank, reducing the amount of heat loss.
- **Water Connections**—3/4" NPT factory installed true dielectric fittings.
- **Factory Installed Heat Traps**—Design incorporates a flexible disk that reduces heat loss in piping and eliminates the potential for noise generation.
- **Protective Magnesium Anode Rod**
- **3/4" NPT Side Connections.**
- **Pedestal Base**
- **T&P Relief Valve**—Installed.
- **Full Port Brass Drain Valve**—Durable tamper proof design.

Commercial Power Vent Gas Water Heater



Light Duty TTW®4 Energy Saver Models

NATURAL GAS AND LIQUID PROPANE GAS

Meet or exceed ASHRAE 90.1b (current standard) C.E.C. Listed
80% Recovery Efficiency

Model Number	Capacity		Nat. BTU/Hr. Input	LP BTU/Hr. Input	Recovery 100°F Rise*				A Floor to Vent Conn.	B Jacket Dia.	C Vent Size	D Floor to T&P Conn.	E Floor to Gas Conn.	F Floor to Space Heating Return in.	G Floor to Space Heating Outlet in.	H Floor to Heater Top in.	J Floor to Water Conn. in.	K Depth in.	Approx. Shipping Weight lbs.
	U.S. Gal.	Imp. Gal.			Nat. U.S. GPH	Nat. Imp. U.S. GPH	LP U.S. GPH	LP Imp. U.S. GPH	in.	in.	in.	in.	in.	in.	in.	in.	in.	in.	
TW4-50S-67FB-3N	48	40	67,000	60,000	65	54	58	49	65%	22	3	50%	11%	13%	50%	56%	57%	26%	188
TW4-65S-70FB-3N	65	54	70,000	63,000	68	57	61	51	69	24	3	53%	11%	13%	53%	59%	60%	28%	222
TW4-75S-76B-3N	75	62	76,000	75,500	74	61	73	60	68%	26	3	53	15	17%	53	60%	61%	31	257

Model Number	Capacity		Nat. kW Input	LP kW Input	Recovery 56°C Rise*		A Floor to Vent Conn.	B Jacket Dia.	C Vent Size	D Floor to T&P Conn.	E Floor to Gas Conn.	F Floor to Space Heating Return mm.	G Floor to Space Heating Outlet mm.	H Floor to Heater Top mm.	J Floor to Water Conn. mm.	K Depth mm.	Approx. Shipping Weight kg.
	Liters				Nat. Liters/Hour	LP Liters/Hour	mm.	mm.	mm.	mm.	mm.	mm.	mm.	mm.	mm.	mm.	
TW4-50S-67FB-3N	182		19.6	17.6	246	220	1673	560	76	1273	320	343	1273	1432	1467	679	85
TW4-65S-70FB-3N	246		20.5	18.5	257	231	1753	610	76	1360	320	343	1360	1511	1543	730	101
TW4-75S-76B-3N	284		22.3	22.1	280	276	1737	660	76	1346	381	451	1346	1530	1562	787	117



Propane models feature a Titanium Stainless Steel propane burner. For Propane (LP) models change suffix "B" to "S" and "N" to "X".

For 5 year models, change suffix from "3" to "5".

*Based on manufacturers rated recovery efficiency.

110 V.A.C. Required for Power Venting / 110 V.A.C. 60HZ 3.1 Amperes.

NSF construction available.



	TW4-50S-67 TW4-65S-70 TW4-75S-76	3" Vent Pipe	4" Vent Pipe
Max. Equivalent Length		†60 ft. **	†180 ft.
Min. Equivalent Length		7 ft.	15 ft.
Number of 90° Elbows	1	55 ft.	175 ft.
	2	50 ft.	170 ft.
	3	45 ft.	165 ft.

Subtract 5ft. for each additional 90° elbow

†For high altitude installations, consult the installation instructions.

**TW4-75S Max. 3" vent length is 50ft.

Meets NAECA Requirements.

General

All gas water heaters are certified at 300 PSI (2068 kPa) test pressure and 150 PSI (1034 kPa) working pressure.

All water connections are 3/4" NPT (19mm) on 11" (279mm) centers, all gas connections are 1/2" (13mm).

All models design certified by CSA International (formerly AGA/CGA), ANSI Z-21.10.1 and/or 10.3 and peak performance rated.

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.

Suitable for Water (Potable) Heating and Space Heating

Toxic chemicals, such as those used for boiler treatment, shall NEVER be introduced into this system. This unit may NEVER be connected to any existing heating system or component(s) previously used with a non-potable water heating appliance.



For U.S. and Canada field service, contact your professional installer or local Bradford White sales representative.

Sales 800-523-2931 • Fax 215-641-1670 / Technical Support 800-334-3393 • Fax 269-795-1089 • Warranty 800-531-2111 • Fax 269-795-1089

International: Telephone 215-641-9400 • Telefax 215-641-9750 / www.bradfordwhite.com

BRADFORD WHITE-CANADA INC. Sales / Technical Support 866-690-0961 / 905-238-0100 • Fax 905-238-0105 / www.bradfordwhite.com

Built to be the Best™

©2011, Bradford White Corporation. All rights reserved.