Electronic Faucet 590T0 & 590T1 Series





Specification: (example)

• Battery (4 'C' cell) or Hardwire (24 VAC) infrared electronic handwash system

- H₂Optics[™] technology no external adjustments required
- Chrome plated one piece CAST Hi-Rise spout with integral sensor
- Adjustable sensing range and timeout
- Audible low battery indicator
- Forged brass solenoid valve (control box No. 0 only)

with... (specify battery or hardwire) with... (add spout required) with... (add outlet required)

• Tempered water supplied to solenoid valve, (except control box options No. 0 and 1)

with... (add control box required) with... (transformer - specify separately - See Back Page)



gineer/Architect Approval		
1odel Specified:		
Approval:	Date:	

DESCRIPTION	PRODUCT NO.		
Hardwire	590T0		
Battery Operated	590TI		





SPOUT & SENSOR	OUTLET	CONTROL BOX
	<u> </u>	✓
0	o	Base Model with Surface Mount Housing* SEE Specification Drawing #13
Single Hole Deckmount Hi-Rise Spout with Integral Sensor	1	For RECESSED MOUNTING Components ASSEMBLED in 10" Box w/S/S Cover.* SEE Specification Drawing #14
Deckmount Hi-Rise Spout with Integral Sensor and 4" Forged Coverplate	Vandal Resistant 1.5 USGPM (5.7 L/min.) Laminar w/Agion ^a Antimicrobial	2
3	Vandal Resistant 1.5 USGPM (5.7 L/min.) Flow Control Aerator	3
4	4	4
5	Vandal Resistant 0.5 USGPM (1.9 L/min.) Flow Control Non- Aerating Spray Outlet	5
6	Vandal Resistant 1.0 USGPM (3.8 L/min.) Flow Control Non- Aerating Spray Outlet	For RECESSED MOUNTING Components & Mechanical Mixing Valve (1) ASSEMBLED in 10" Box w/S/S Cover. SEE Specification Drawing #15
7	7	7
Deckmount Hi-Rise Spout with Integral Sensor and 8" Forged Coverplate	8	For RECESSED MOUNTING Components & Thermostatic Mixing Valve ASSEMBLED in 10" Box w/S/S Cover. SEE Specification Drawing #16
9	9	9

Flowrates are at 60 PSI.

^{*} Mixing Valve supplied by others.

⁽¹⁾ With Thermostatic Limit Stop.



Approvals:

- CSA certified
- Complies to ASME A112.18.1
- ADA Compliant and meets
 Handicapped Accessibility
 Standard ASME A117.1 of less than
 5 lbs. handle operating force.
- IAPMO listed
- Control Box Option 6 Mechanical Mixing Valve CSA certified
- Control Box Option 8 Thermostatic Mixing Valve CSA certified and meets ASSE 1016 and 1017

(Contact Delta Representative for State and/or Local Approvals.)
U.S. Patent #6, 826, 455.

FLOWRATE vs PRESSURE FLOW **Outlet Flowrates** (l/min.) (USGPM) 8 2 2 10 20 30 40 50 60 Line Pressure (psig) **Spout Outlets** No. 3 Aerator No. 2 Laminar Flow Outlet ■ ■ No. 6 Flow Control Outlet


OPERATION:

- Hands free (touchless) operation.
- · Water flows when sensor is activated.
- Water flow stops upon de-activiation of sensor.
- Auto shut-off feature that is selectable between 15 to 75 seconds. Factory set to 45 seconds. Will reset once obstruction is removed.
- Adjustable sensing distance 76 to 381mm (3" to 15") factory set to 229mm (9") (+/- 1.0")
- Low battery audible beep (for battery models only) will activate after faucet shuts off when approximately 1500 cycles remain.

NOTE: For optimum performance of this product, we recommend a system pressure between 20 and 80 PSI static. This product will operate up to a maximum of 125 PSI static per ANSI and CSA requirements. However, we do not recommend pressures above 80 PSI. Thermal expansion or leaking pressure reducing valves may require use of expansion tanks or relief valves to ensure your system never exceeds its maximum intended pressure setting.

TECK®

Electronic Faucet 590T0 & 590T1 Series



590T0 & 590TI ELECTRONIC FAUCET OPTIONAL ACCESSORIES:

/	TRANSFORMERS:				
	060704A	110 to 24VAC Class II 20VA (Up to 5 Electronic Valves)			
	060771A	110 to 24VAC Class II 40VA (Up to 10 Electronic Valves)			
	060772A	110 to 24VAC Class II 100VA (Up to 25 Electronic Valves)			
V	CORDS:				
	060690A	36" Cable Extension			

Note: Measurements may vary - 6mm (0.25")

Refer to www.specselect.com for individual models.

Product supplied as shown by solid lines. All items shown by dotted lines supplied by others.