



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
10.00"	5.50"	7.00"
<u>BP Height</u>	<u>BP Width</u>	
6.50"	4.76"	
<u>Hanging Weight</u>		
2.43 lb		

Lamping:

Incandescent MB	1,150 Rated Lumens
1.00 60W MB	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.17 lb	7.87"	9.45"	9.06"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209054271	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)
Lighting Direction: Both