

Certifications

This is to verify that products manufactured by Charlotte Pipe and Foundry, Cast Iron Division, are manufactured in the United States and conform to the following standards:

SERVICE HUB AND SPIGOT PIPE AND FITTINGS

All cast iron soil pipe and fittings shall be marked with the collective trademark of the Cast Iron Soil Pipe Institute (CISPI). ASTM A 74

Listed by NSF® International to the UP Code ISO 9001:2015 Certified

EXTRA HEAVY HUB AND SPIGOT PIPE AND FITTINGS

All cast iron soil pipe and fittings shall be marked with the collective trademark of the Cast Iron Soil Pipe Institute (CISPI). ASTM A 74

Listed by NSF® International to the UP Code ISO 9001:2015 Certified

NO-HUB PIPE AND FITTINGS

All cast iron soil pipe and fittings shall be marked with the collective trademark of the Cast Iron Soil Pipe Institute (CISPI). CISPI Standard 301 **ASTM A 888** Listed by NSF® International to the UP Code ISO 9001:2015 Certified

NO-HUB STANDARD COUPLINGS

CISPI Standard 310 **ASTM C 1277** Certified by NSF® International

NO-HUB HEAVY DUTY (MD) COUPLINGS

ASTM C 1540 Factory Mutual 1680

NO-HUB HEAVY DUTY (HD) COUPLINGS

ASTM C 1540 Factory Mutual 1680

COMPRESSION GASKETS

ASTM C 564 CISPI HSN 85

Very truly yours,

Hooper Hardison, President

Notary Public

LC-CI (10-15-19)

My commission expires July 02, 2022

Hope Handson

Veri L. Wilson

TERRIL WILSON NOTARY PUBLIC UNION COUNTY, NC My Commission Expires 7-2-2022





Reference Standards Cast Iron

AMERICAN SOCIETY FOR TESTING AND MATERIALS

ASTM	TITLE
A 74 SCOPE:	SPECIFICATION FOR CAST IRON SOIL PIPE AND FITTINGS HUB AND SPIGOT (SERVICE AND EXTRA HEAVY) THIS SPECIFICATION COVERS CAST IRON PIPE AND FITTINGS USED IN SANITARY DRAIN, WASTE, AND VENT (DWV), SEWER, AND STORM DRAINAGE APPLICATION. THIS SYSTEM IS INTENDED FOR USE IN NONPRESSURE APPLICATIONS.
C 564 SCOPE:	SPECIFICATION FOR RUBBER GASKETS FOR CAST IRON SOIL PIPE AND FITTINGS THIS SPECIFICATION COVERS PREFORMED RUBBER GASKETS USED TO SEAL JOINTS IN CAST IRON SOIL PIPE AND FITTINGS.
C 1277 SCOPE:	SPECIFICATION FOR COUPLING FOR USE IN CONNECTION WITH HUBLESS CAST IRON PIPE AND FITTINGS FOR SANITARY AND STORM DRAIN, WASTE, AND VENT PIPING APPLICATION (REGULAR HUBLESS COUPLING) THE PURPOSE OF THIS SPECIFICATION IS TO ESTABLISH CRITERIA FOR MATERIAL DIMENSIONS AND TOLERANCES FOR ONE TYPE OF COUPLING USED IN HUBLESS CAST IRON SOIL PIPE AND FITTING FOR SANITARY AND STORM DRAIN, WASTE AND VENT PIPING APPLICATIONS.
C 1540 SCOPE:	SPECIFICATION FOR SHIELDED COUPLINGS JOINING HUBLESS CAST IRON SOIL PIPE AND FITTINGS (HEAVY DUTY COUPLINGS) THIS SPECIFICATION COVERS THE EVALUATION OF THE PERFORMANCE OF SHIELDED HUBLESS COUPLINGS TO JOIN CAST IRON SOIL PIPE AND FITTINGS.

CAST IRON SOIL PIPE INSTITUTE

CISPI	TITLE
301	SPECIFICATION FOR HUBLESS CAST IRON SOIL PIPE AND FITTINGS FOR SANITARY AND
SCOPE:	STORM DRAIN, WASTE, AND VENT PIPING APPLICATIONS THE PURPOSE OF THIS STANDARD IS TO ESTABLISH STANDARDS COVERING MATERIAL, DIMENSIONS, AND TOLERANCE FOR PIPE AND FITTINGS FOR HUBLESS CAST IRON SANITARY AND STORM DRAIN, SANITARY WASTE, AND VENT PIPING APPLICATIONS.
310	SPECIFICATION FOR COUPLING FOR USE IN CONNECTION WITH HUBLESS CAST IRON PIPE AND FITTINGS FOR SANITARY AND STORM DRAIN, WASTE, AND VENT PIPING APPLICATION (REGULAR HUBLESS COUPLING)
SCOPE:	THE PURPOSE OF THIS SPECIFICATION IS TO ESTABLISH CRITERIA FOR MATERIAL DIMENSIONS AND TOLERANCES FOR ONE TYPE OF COUPLING USED IN HUBLESS CAST IRON SOIL PIPE AND FITTING FOR SANITARY AND STORM DRAIN, WASTE AND VENT PIPING APPLICATIONS.



PART NO. NH 50

	Blind Plug	
Size	F	Weight
11/2	13/4	0.6
2	13/4	0.7
3	13/4	1.1
4	13/4	2.0
5	13/4	2.9
6	13/4	3.2
8	21/4	6.5
10	3	14.7
12	31/2	17.6
15	31/2	28.0
15	31/2	28.0



PART NO. NH 52

Tapped Ferrule Less Brass Plug and PART NO. NH 52S


Tapped Ferrule with Southern
Raised-Head Brass Plug Installed

Raised-Head Brass Plug Installed							
Size	F	IPS Tapping	Weight				
2	23/16	11/2	0.9				
3	23/16	21/2	1.9				
4	23/16	31/2	2.5				
5	41/2	4	6.5				
6	41/2	5	8.0				
8	41/2	6	12.1				




PART NO. NH 53

Single Two-Way Cleanout							
Size	E	F	Weight				
4	71/2	15	16.0				



PART NO. NH 53A


Two-Way Cleanout							
Size	D	E	F	G	Weight		
4	81/4	23/4	12	61/2	15.0		



PART NO. NH 54

Two-Way Baffle Cleanout


ino nag barno cicanoat							
Size	D	F	Weight				
3 x 3 x 4	15	9	14.2				
4 x 4 x 4	183/8	91/2	22.0				





PART NO. NH 56

Notched and Slotted Closet Collar

Size	D	Е	F	Α	Weight
4 x 3	31/2	33/8	71/4	47/32	3.3
4 x 3	8	327/64	71/4	4	6.1
4 x 4	4	43/8	71/4	49/64	4.7
4 x 4	8	43/8	71/4	47/32	7.0







4 x 4 4" **l**ong

PART NO. NH 57

Horizontal Twin Tapped Tee

	HUITZUIILAI	IWIII	iappeu	166	
Size	Α	D	F	Н	Weight
3 x 1½	13/8	4	7	3	7.3
4 x 11/2	13/2	4	7	3	8.0



PART NO. NH 457

Vented Closet Tee with 2" Top Vent

(Left or Right; Designed for use below the floor;

ricting does not require a partie)							
Size	В	С	D	Ε	F	G	Wt.
4x4x2x4(L)	41/4	51/4	33/4	4	101/2	33/4	12.1
4x4x2x4(R)	41/4	51/4	33/4	4	101/2	33/4	11.

