

# SELECT<sup>®</sup> High Efficiency

## High-Efficiency Residential Electric Water Heaters



**New, Higher Energy Factor of .93, meets efficiency requirements for most electric utility rebate programs** — 2-1/2"-thick CFC-free foam insulation, heat trap nipples and other features produce performance that meets Energy Star Home Program recommendations and California Title 24 requirements.

**Diffuser Dip Tube** — Helps reduce lime and sediment buildup, maximizes hot water output. Made of State PEXAN,<sup>™</sup> a cross-link PEX polymer that can withstand long-term exposure to water temperatures up to 400°F.

**Aluminum Anode Rod** — Helps protect against corrosion for longer life.

**Durable Tamper-Resistant Brass Drain Valve**

**Glass-Lined Tank** — For long-lasting protection against rust and corrosion.

**Upgrade Tank Warranty to 10 Years** — See details on page 2.

**Factory-Installed Side-Mounted Temperature & Pressure (T&P) Relief Valve** — Top-mounted T&P Valve available as option on some models.

**6-Year Limited Tank and Parts Warranty**

**Code Compliance** — All models meet or exceed federal minimum energy standards effective January 20, 2004, according to latest editions of the National Appliance Energy Conservation Act (NAECA). They also comply with the latest editions of the BOCA National Codes, CEC, UBC, SBCC, CABO and HUD standards. All models UL Listed according to safety specifications outlined in Underwriters Laboratories Inc. Standards for Safety (UL 174).



For more information on Select<sup>®</sup> contact:  
State Water Heaters  
500 Tennessee Waltz Parkway, Ashland City, TN 37015  
**800-365-0024 Toll-free USA**  
[www.statewaterheaters.com](http://www.statewaterheaters.com)

SRESS00606

March 2008R

**SOLID.STATE.**



# SELECT<sup>®</sup> High Efficiency

## High-Efficiency Residential Electric Water Heaters




MODEL NUMBER	PEAK DEMAND OUTPUT (1st Hour Rating Gallons)	ENERGY FACTOR	GALLON CAPACITY	ELEMENT WATTAGE 240 VAC		RECOVERY 90°F RISE	R VALUE	DIMENSIONS IN INCHES			APPROX. SHIPPING WEIGHT (LBS)
				STANDARD	MAXIMUM			A HEIGHT	B DIAMETER	C	
TALL MODELS											
ES6 40 DOCT	54	.93	40	4500	6000	21	20	60	19	53-1/2	120
ES6 52 DOCT *	60	.93	50	4500	6000	21	20	56-1/2	21-1/2	47-1/2	135
ES6 66 DOCT	76	.92	66	4500	6000	21	20	61	23	53	180
ES6 80 DOCT *	87	.93	80	4500	6000	21	20	61-1/2	25	52	210
MEDIUM MODEL											
ES6 50 DOCS	62	.93	50	4500	6000	21	20	49	23	40-1/2	155

Recoveries are rounded to nearest gallon

Water Connections - 3/4" male NPT on all models

For 10-Year Tank Warranty, change "6" to "X" in Model Number (ES X 40 DOCT)

\*Models not available with top-mounted T&P Valve



\*Location for optional top-mounted T&P Valve, if available and ordered from factory.

For complete information on limited warranties, consult written warranty, or contact the State Customer Care Center, 1-800-365-0024.

State Industries, Inc. reserves the right to make product changes or improvements without prior notice.

For more information on Select<sup>®</sup> contact:  
State Water Heaters  
500 Tennessee Waltz Parkway, Ashland City, TN 37015  
**800-365-0024 Toll-free USA**  
[www.statewaterheaters.com](http://www.statewaterheaters.com)

**SOLID. STATE.**

