

## Submittal Data

PROJECT:	UNIT TAG:	QUANTITY:	
	TYPE OF SERVICE:		
REPRESENTATIVE:	 SUBMITTED BY:	DATE:	
ENGINEER:	APPROVED BY:	DATE:	
CONTRACTOR:	ORDER NO.:	DATE:	
ENGINEER:	SUBMITTED BY: APPROVED BY:	DATE:	



## UP 15-29 SU


Circulator pumps


Product photo could vary from the actual product

Conditions of Service	Pump Data		Motor Data	
Flow: Head: Efficiency: Liquid: Temperature: NPSH required: Viscosity: Specific Gravity:	Maximum operating pressure: Liquid temperature range: Maximum ambient temperature: Approvals: Type of connection: Flange standard: Pipe connection: Product number:	145 psi 35.6 230 °F 104 °F UL, CSA S.S. Union USA Threaded 1 1/4" NPSM 59896775	Max. power input: Rated power - P2: Rated voltage: Main frequency: Insulation class: Motor protection: Thermal protection:	87 W 0.121 HP 115 V 60 Hz F Contact internal









## Materials:


Pump housing: Stainless steel


DIN W.-Nr. 1.4301

AISI 304

Impeller: Composite, PES

## 59896775 UP 15-29 SU 60 Hz





Note! All units are in [mm] unless others are stated. Disclaimer: This simplified dimensional drawing does not show all details.