



PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 67003
DESCRIPTION: 18/4 STRANDED SHIELDED CMR/CL3R/FPLR
CONSTRUCTION: This cable consists of four bare copper insulated conductors with an overall shield with a drain. The overall assembly has an overall jacket.
APPROVALS: UL Standard 13 and 444, NEC Articles 725 and 800.
APPLICATION: Class 3 Power Limited Circuit Cable and Communications Cable for Riser Applications

Construction Parameters:

Conductor	18 AWG Bare Copper
Stranding	7/.0152"
Insulation Material	PVC
Insulation Thickness	0.008" Nom.
Insulated Conductor Diameter	0.062" Nom.
Number of Conductors	4
Lay Length	4.00" Nom.
Shield	Alum/Mylar
Drain	24 AWG Solid Tinned Copper
Jacket Material	PVC
Jacket Thickness	0.017" Nom.
Overall Cable Diameter	0.196" Nom.
Approximate Cable Weight	33.6 Lbs/1M' Nom.
Flame Rating	UL 1666 Riser Flame Test

Cable Cross-Section



Electrical & Environmental Properties:

Temperature Rating	-20°C to 60°C
Operating Voltage	300 V RMS Max.
Capacitance Between Conductors @ 1 KHz	59 pF/ft Nom.
Capacitance Between Conductors to Shield @ 1 KHz	109 pF/ft Nom.
DC Resistance per Conductor @ 20°C	6.29 Ohms/1M' Nom.

Insulation Colors	Black Red White Green
Jacket Color	Gray (Other colors available for minimum order)

Legend (Surface Ink Print) CCI 67003 * 18 AWG 4/C C(ETL)US (ETL CODE) TYPE CMR/CL3R/FPLR SUN RES -
- CMX OUTDOOR - TYPE CMG FT4 -- XX/XX/XX (MONTH/DAY/YEAR) XXXXXX
(W/O #) P-07-KA120011-MSHA 300V

This product complies with European Directive 2011/65/EU (RoHS-2)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal. The jacket is sequentially footmarked.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Specification Issue Date: January 10, 2014