# ASTM Ecoflex<sup>®</sup> Potable PEX Twin

uponor

Submittal Information Revision A: Dec. 20, 2010

## Project Information

## Joh Name

Job Name:		
Location:	Part No. Ordered:	
Engineer:	Date Submitted:	
Contractor:	Submitted By:	
Manufacturer's Representative:	Approved By:	

### **Technical Data**

Service Pipe: Crosslinked polyethylene (PEX-a) Engel method; PEX 5006; NSF- certified SDR-9								
Insulation:	Multilayered, closed-cell, crosslinked polyethylene (PEX) foam insulat with a thermal conductivity of 0.26 BTU in./sq.ft./hour/°F; vapor permeability of 0.1g/100 sq. in./day							
Jacket:	Corrugated, seamless high-density polyethylene (HDPE); UV-protected							
Operating Limits:	200°F at 80 psi (93°C at 5.5 bar) 180°F at 100 psi (82°C at 6.9 bar) 73°F at 160 psi (23°C at 11.0 bar)							
Due doest Information and Application Use								

## **Product Information and Application Use**

The ASTM Ecoflex<sup>®</sup> Potable PEX Twin product features two Uponor AquaPEX<sup>®</sup> service pipes protected by multilayer PEX-foam insulation and covered by a corrugated, waterproof HDPE jacket. Use ASTM Ecoflex Potable PEX Twin for hot and cold potable-water applications.



✓	Description	Part Number	Service Pipe O.D.	Service Pipe I.D.	Foam Thickness	Insulation Value	Bend Radius	Weight (lbs./ft.)
	1" Potable PEX Twin with 6.9" Jacket, 600-ft. coil	5226910	1.125"	0.862"	1.54"	R-5.70	20"	1.30 lbs.
	1¼" Potable PEX Twin with 6.9" Jacket, 500-ft. coil	5226913	1.375"	1.054"	1.34"	R-4.96	28"	1.40 lbs.
	$1^{1\!\prime_2}$ " Potable PEX Twin with 6.9" Jacket, 300-ft. coil	5226915	1.625"	1.244"	1.06"	R-3.93	32"	1.55 lbs.
	2" Potable PEX Twin with 7.9" Jacket, 300-ft. coil	5227920	2.125"	1.629"	1.06"	R-3.93	40"	2.68 lbs.

#### Installation

Install Ecoflex Potable PEX in hot or cold potable-water applications. Join pipes using Uponor ProPEX<sup>®</sup> or WIPEX<sup>TM</sup> fittings.<sup>1</sup> Ecoflex End Caps are required on all exposed ends of Ecoflex pipes to avoid ground water contamination. For additional information, refer to the Uponor Pre-insulated Pipe Systems Design and Installation Manual.

#### Standards

CSA B137.5; ASTM F876; ASTM F877; ASTM F1960; ASTM F2023; ASTM E84; ASTM E119/UL 263; NSF/ANSI Standard 14; NSF/ANSI Standard 61; AWWA C904<sup>2</sup>

#### Codes

UPC; IPC; NSPC; NPC of Canada

#### Listings

NSF/ANSI 14- and 61-certified; NSF-pw

#### **Related Applications**

Pre-insulated Pipe Systems Permafrost Prevention Systems Plumbing Systems

#### **Contact Information**

Uponor, Inc. 5925 148th Street West Apple Valley, MN 55124 USA Phone: (800) 321-4739 Fax: (952) 891-2008 www.uponor-usa.com Uponor Ltd. 2000 Argentia Road, Plaza 1, Suite 200 Mississauga, ON L5N 1W1 CANADA Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca

 $^1\text{ProPEX}^{\circledast}$  is a registered trademark of Uponor, Inc. ProPEX  $^{'''}$  is a trademark of Uponor Ltd.  $^2\text{This}$  standard applies to 3/4 Uponor AquaPEX tubing and larger.