

SPECIFICATIONS

G15




 SCHIER MODEL	Capacity			Pipe Sizes			Rough-in Dimensions (in.)									Poly Cover Load Rating (lbs.)	Weight (lbs.)	
	Flow Rate (GPM)	Grease (lbs.)	Liquid (gal.)	Plain End SCH.40		Optional Male Thread (no charge)	Body			Inlet		Outlet					Dry	Wet
				Standard	Optional (no charge)		L	W	H	A	B	C	D	E				
PATG-1412	10	20	5.3	2	3	2, 3	17 ½	15 ¼	15	8 ⅜	6 ⅝	10 ¼	4 ¾	6	500	20	64	
PATG-1815	15	60	10	2	3	2, 3	23 ½	15 ¼	18 ½	11	7 ½	13 ½	5	6	500	30	113	
PATG-15-LO	15	60	10	2	3	2, 3	24 ½	18 ½	10 ¾	6	4 ¾	7 ½	3 ¼	5 ¾	500	35	118	
PATG-1820	20	70	17	2	3	2, 3	25 ½	19 ¼	19 ¼	12	7 ¼	14 ¼	5	6 ¼	500	37	179	
PATG-20-LO	20	80	21	2	3	2, 3	30 ½	24 ½	13 ¾	6 ½	7 ¼	10 ¼	3 ½	5 ¾	500	50	225	
PATG-2025	25	98	28	3	2	2, 3	29 ¾	23 ½	23 ¼	13	10 ¼	16	7 ¼	6 ⅞	500	63	297	
PATG-2420	30	109	31	3	2	2, 3	29 ¾	23 ½	23 ¼	14 ½	8 ¾	17 ⅞	5 ⅝	6 ⅞	500	63	322	
PATG-30-LO	30	90	23	3	2	2, 3	34 ½	24 ½	13 ¾	6 ½	7 ¼	10 ¼	3 ½	5 ¾	500	55	247	
PATG-2635	35	120	40	3	4	3, 4	29 ¾	23 ½	28 ½	16 ½	12	21	7 ½	6 ⅞	500	75	409	
PATG-35-LO	35	98	28	3	2	2, 3	40 ½	24 ½	13 ¾	6 ½	7 ¼	10 ¼	3 ½	5 ¾	500	65	298	
PATG-2824	40	180	54	4	3	3, 4	31 ¾	26	32 ½	21 ½	11	25 ¾	6 ¾	6 ⅞	500	82	532	
PATG-3050	50	259	60	4	3	3, 4	35 ¼	26	32 ½	21 ½	11	25 ¾	6 ¾	6 ⅞	500	94	594	
PATG-50-LO	50	128	41	3	4	3, 4	54	24 ¾	16 ¼	6 ¾	9 ½	11	5 ¼	12	500	70	412	
PATG-3224	60	288	67	4	3	3, 4	38 ¾	26	32 ½	21 ½	11	25 ¾	6 ¾	6 ⅞	500	105	664	
PATG-3475	75	300	80	4	3	3, 4	39	28 ½	32 ½	22	10 ½	26 ¼	6 ¼	6 ⅞	500	105	772	
PATG-3628	100	350	110	4	3	3, 4	41 ¼	35 ½	32 ½	22	10 ½	26 ¼	6 ¼	6 ⅞	500	162	1,080	



Models PATG-2025 & PATG-3050 are certified to ASME A112.14.3 and listed by IAPMO. All other models are manufactured to conform to that standard.

PATG-1412 through PATG-3628

Low Profile Model (-LO Suffix)



Engineer Specification Guide

Download Schier CSI MasterSpec language at schierproducts.com/literature.html

Schier Trapper II™ grease interceptor model # _____ shall be lifetime guaranteed and made in USA of seamless, rotationally-molded High Density Polyethylene with minimum 3/8" uniform wall thickness. Interceptor shall be furnished for above or below grade installation. Interceptor shall be built in accordance to ASME A112.14.3 (type C), with built-in flow control, built-in test caps and three outlet options. Interceptor flow rate shall be _____ GPM. Interceptor grease capacity shall be _____ lbs. Cover shall provide water/gas-tight seal and have minimum 500 lbs load capacity.

LIST PRICES

G16

 SCHIER MODEL	Base Unit	Bolt-On Risers (dimensions shown from top of unit)				Standard Poly Cover	1/4" Steel Tread Cover		Recessed for Tile Steel Cover		May Ship Parcel
		4" to 24"		>24" to 36"			Part #	Price	Part #	Price	
		Part #	Price	Part #	Price						
PATG-1412	\$584	R1412-424	\$712	R1412-2436	\$948	Included	CS1412	\$436	CSR1412	\$762	✓
PATG-1815	\$750	R1815-424	\$764	R1815-2436	\$1,056	Included	CS1815	\$668	CSR1815	\$1,104	✓
PATG-15-LO	\$958	n/a	n/a	n/a	n/a	Included	n/a	n/a	n/a	n/a	✓
PATG-1820	\$848	R1820-424	\$902	R1820-2436	\$1,200	Included	CS1820	\$818	CSR1820	\$1,372	✓
PATG-20-LO	\$1,266	n/a	n/a	n/a	n/a	Included	n/a	n/a	n/a	n/a	✓
PATG-2025	\$1,012	R2025-424	\$824	R2025-2436	\$1,388	Included	CS2025	\$968	CSR2025	\$1,640	✓
PATG-2420	\$1,012	R2420-424	\$824	R2420-2436	\$1,388	Included	CS2420	\$968	CSR2420	\$1,640	✓
PATG-30-LO	\$1,508	n/a	n/a	n/a	n/a	Included	n/a	n/a	n/a	n/a	✓
PATG-2635	\$1,320	R2635-424	\$824	R2635-2436	\$1,388	Included	CS2635	\$968	CSR2635	\$1,640	✓
PATG-35-LO	\$1,694	n/a	n/a	n/a	n/a	Included	n/a	n/a	n/a	n/a	✓
PATG-2824	\$1,530	R2824-424	\$910	R2824-2436	\$1,690	Included	CS2824	\$1,122	CSR2824	\$1,908	
PATG-3050	\$1,618	R3050-424	\$1,006	R3050-2436	\$1,886	Included	CS3050	\$1,122	CSR3050	\$1,908	
PATG-50-LO	\$2,256	n/a	n/a	n/a	n/a	Included	n/a	n/a	n/a	n/a	
PATG-3224	\$2,178	R3224-424	\$1,102	R3224-2436	\$2,076	Included	CS3224	\$1,272	CSR3224	\$2,176	
PATG-3475	\$2,530	R3475-424	\$1,136	R3475-2436	\$2,134	Included	CS3475	\$1,384	CSR3475	\$2,368	
PATG-3628	\$3,026	R3628-424	\$1,518	R3628-2436	\$2,892	Included	CS3628	\$1,686	CSR3628	\$3,380	

