

FLUENCE_®

Features


- CleanCoat_® glass coating
- Continuous door panel guide mechanism for smooth, quiet sliding action
- Out-of-plumb adjustability allows for easy installation
- Stainless steel hardware prevents rusting or corrosion
- · Gently curved inside and outside towel bar
- Smooth, easy-to-clean wall jambs
- 1/4" (6 mm) thick tempered glass

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1 (tempered glass)
- 16 CFR Part 1201

SLIDING BATH/SHOWER DOORS K-702200 ALSO K-702202, K-702204, K-702206



Glass Options

- L: Clear
- G53: Rhapsody
- G54: Falling Lines

Frame Finishes/Colors

SHP: Polished Silver

MX: Matte Nickel

• ABV: Brushed Bronze

Specified Model

Model	Application	Glass O	Glass Options			Frame Finishes/Colors		
K-702200	Bath	□ L*	□ G53	□ G54*	□ SHP	□ MX	□ ABV	
K-702202	Bath	□ L*	□ G53	□ G54*	□ SHP	□ MX	□ ABV	
K-702204	Bath	□ L*	□ G53	□ G54*	□ SHP	□ MX	□ ABV	
K-702206	Shower	□ L*	□ G53	□ G54*	□ SHP	□ MX	□ ABV	
K-702208	Shower	□ L*	□ G53	□ G54*	□ SHP	□ MX	□ ABV	
K-702211	Bath	□ L*			□ SHP			
K-702213	Shower	□ L*			□ SHP			
K-702215	Shower	□ L*			□ SHP			
K-702219	Shower	□ L*			□ SHP			
K-702221	Shower	□ L*			□ SHP			


Product Specification

FLUENCE_®

Installation Notes

Install this product according to the installation guide.

Roughing-In Notes						
Model	A (Max)	В	C (Walk Through)			
K-702200	59-5/8" (1514 mm)	58-5/16" (1481 mm)	27-7/8" (708 mm)			
K-702202	57" (1448 mm)	55-3/4" (1416 mm)	26-5/8" (676 mm)			
K-702204	59-5/8" (1514 mm)	55-3/4" (1416 mm)	27-7/8" (708 mm)			
K-702206	59-5/8" (1514 mm)	70-5/16" (1802 mm)	27-7/8" (708 mm)			
K-702208	47-5/8" (1210 mm)	70-5/16" (1802 mm)	21-7/8" (556 mm)			
K-702211	52" (1321 mm)	63" (1600 mm)	24" (610 mm)			
K-702213	43" (1092 mm)	70" (1778 mm)	19-1/2" (495 mm)			
K-702215	47-1/2" (1207 mm)	76-1/2" (1943 mm)	21-7/8" (556 mm)			
K-702219	40" (1016 mm)	76" (1930 mm)	18" (457 mm)			
K-702221	52" (1321 mm)	76" (1930 mm)	24" (610 mm)			



Product Diagram

