

Features

- Metal construction.
- Katalyst® Spray Technology with air induction ball joint (patent pending).
- Single-function spray with 48 individual MasterClean™ spray nozzles.
- Push-button diverter.
- Three color options included for showerhead trim ring - white, green, or black.
- Requires a Rite-Temp® valve.
- Complements Toobi® Suite.
- 2.0 gal/min (7.6 l/min) maximum flow rate.

Required Accessories

- K- 304-K Pressure-balancing Valve Less Stops
or
K- 304-US Pressure-balancing Valve With Stops
or
K- 304-PS Pressure-balancing Valve With Stops
or
K- 304-PX Pressure-balancing Valve Less Steps
or
K- 304-UX Pressure-balancing Valve Less Stops
or
K- 304-KS Pressure-balancing Valve With Stops
or
K- 2971-KS 3/4" Pressure-balancing Valve
or
K- 11748-KS Pressure-Balancing Valve w/Diverter
or
K- 11748-K Pressure-Balancing Valve w/Diverter

Optional Accessories

1151968 Roughing-In Kit



Codes/Standards



ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel



Technical Information

All product dimensions are nominal.

Showerhead:

Rated maximum flow: 2 gal/min (7.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.

Install Rite-Temp valve according to valve installation guide.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Cap shower outlet if deck-mounted spout, diverter, or handshower is connected to the spout outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between valve and wall-mount spout.