•TRUSTED QUALITY SINCE 1921•

SPECIALTY

SPECIALTY APPLIANCE EPOXY SPRAYS

DESCRIPTION AND USES

Appliance epoxy is a hard, moisture resistant enamel that is specifically formulated for indoor metal surfaces. It provides a smooth, washable surface for refinishing the exterior of appliances such as refrigerators, dishwashers, laundry machines, dryers and other indoor metal applications such as tables or cabinets.

PRODUCTS

FINISHES

210372	Biscuit
7881830	White
7882830	Almond
7886830	Black
7887830	Stainless Steel

PAINTING CONDITIONS

Use outdoors or in a well ventilated area such as an open garage. Not intended for continuous water immersion or for surfaces that, when heated, exceed 200°F (93°C). Priming is not recommended. Do not use on objects exposed to heat (eg., stovetops, oven interiors, etc.).

PRODUCT APPLICATION

SURFACE PREPARATION

Remove all dirt, grease, oil, salt and chemical contaminants by washing the surface with a commercial detergent, or other suitable cleaning method. Rinse with fresh water and allow to thoroughly dry. Remove loose paint and rust with wire brush or sandpaper. Lightly sand glossy surfaces.

APPLICATION

Apply only when air and surface temperatures are between 50-90°F (10-32°C) and the relative humidity is below 85% to ensure proper drying. Avoid spraying in very windy or dusty conditions. Cover surrounding area to protect from overspray. Overspray can carry a significant distance. Shake can vigorously for one minute after the mixing ball begins to rattle. Shake often during use. Hold can upright 12-16" from surface and spray in a steady back-andforth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. Apply several light coats a few minutes apart to avoid drips and runs. **Do not use near open flame.**

CLEAN-UP

Clean valve immediately after use by turning can upside down and depressing spray button for 3-5 seconds (some paint will be sprayed out, so be careful to not inadvertently spray yourself or other objects). Clean up wet paint with xylene or mineral spirits. Throw away empty can in trash pick-up. Do not burn or place in home trash compactor.

CLOGGING

If the value clogs, twist and pull off spray tip and rinse in a solvent such as mineral spirits. Do not insert any object into can valve opening.

SPC-01



TECHNICAL DATA

SPECIALTY APPLIANCE EPOXY SPRAYS

PHYSICAL PROPERTIES		
		FINISHES
Resin Type		Epoxy Ester Modified Alkyd
Fill Weight		12 oz.
Volatile Organic	Compounds	Maximum 60% by weight
Practical Coverage DFT (assumes 15%		Approximately 7 sq. ft./can (0.63 m²/can)
Dry Times at 70°F (21°C) and 50% Relative Humidity	Tack-free	2-4 hours
	Handle	5-9 hours
	Recoat	Within 30 minutes or after 1 week
Dry Heat Resistance		200°F (93°C)
Shelf Life		5 years
Safety Information	Flash Point	Below 0°F (-18°C)
	Contains	Xylene and Toluene
	Warning!	For additional information, see MSDS.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, Illinois 60061 An RPM Company

Phone: 888•683•5667 www.rustoleum.com Form: 5009790 Rev.: 030311