





Aluminum Cased and Uncased Heat Pump / Cooling Coils 1 1/2 - 5 Ton

4TXA, 4TXC, 4TXC-CC

Heat Pump /Cooling Coils for R-410A



PUB. NO. 22-1813-06



Aluminum Heat Pump Coil Nomenclature

	4	T	X	A	B	0	3	6	B	C	3	H	U	A	A
Refrigerant Type 4 - R410A															
Product Family T-Premium (Heat Pump or Convertible Coil)															
Coil Design X - Direct Expansion Evaporator Coil															
Product Family C - Cased A Coil A - Uncased A Coil F - Cased Horizontal Flat Coil															
Coil Width (Cased/Uncased) A - 14.5" / 13.3" B - 17.5" / 16.3" C - 21.0" / 19.8" D - 24.5" / 23.3" H - 10.5"															
Refrigerant Line Coupling 0 - Braze															
Nominal Capacity in 000's of BTU's															
Major Design Change															
Efficiency C - Standard S - Hi Efficiency															
Refrigerant Control 3 - TXV - Non-Bleed															
Coil Circuitry H - Heat Pump															
Airflow Configuration A - Upflow Only U - Upflow / Downflow H - Horizontal Only C - Convertible - Upflow, Downflow, Left or Right Airflow															
Minor Design Change															
Unit Parts Identifier															



High Efficiency /Staged System Aluminum Heat Pump/ Cooling Coil Nomenclature

	4	T	X	C	B	0	0	1	C	C	3	H	C	A	A
Refrigerant Type 4 - R410A															
Product Family T-Premium (Heat Pump or Convertible Coil)															
Coil Design X - Direct Expansion Evaporator Coil															
Product Family C - Cased A Coil A - Uncased A Coil F - Cased Horizontal Flat Coil															
Coil Width (Cased/Uncased) A - 14.5" / 13.3" B - 17.5" / 16.3" C - 21.0" / 19.8" D - 24.5" / 23.3" H - 10.5"															
Refrigerant Line Coupling 0 - Brazed															
Model Number Distinguisher															
Major Design Change															
Efficiency C - Standard S - Hi Efficiency (Derived from 10 SEER products)															
Refrigerant Control 3 - TXV - Non-Bleed															
Coil Circuitry H - Heat Pump															
Airflow Configuration A - Upflow Only U - Upflow / Downflow H - Horizontal Only C - Convertible - Upflow, Downflow, Left or Right Airflow															
Minor Design Change															
Unit Parts Identifier															



General Data

Optional Accessories

13 SEER Coil Enclosures				
Model Number	Coil Cooling or Heat Pump		Used With Furnaces Flush on Both Sides	Dimensions (in.) H x W x D
BAYCLE14A1422A	4TXAA018BC3HUA 4TXAA024BC3HUA	TXA018C4 TXA024C4 TXA030C4	14-1/2" Wide Furnaces	22-1/2 x 14-1/2 x 21-1/2
BAYCLE17A1722A	4TXAB025BC3HUA 4TXAB031BC3HUA 4TXAB032BC3HUA 4TXAB036BC3HUA 4TXAB042BC3HUA 4TXAB048BC3HUA	TXA025C4 TXA031C4 TXA035C4 TXA036C4 TXA042C4 TXA048C4	17-1/2" Wide Furnaces	22-5/8 x 17-1/2 x 21-1/2
BAYCLE21A2130A	4TXAC037BC3HUA 4TXAC043BC3HUA 4TXAC044BC3HUA 4TXAC049BC3HUA 4TXAC060BC3HUA	TXA037C4 TXA043C4 TXA049C4 TXA060C5 RXA060S3	21" Wide Furnaces	30 x 21 x 21-1/2
BAYCLE24A2430A	4TXAD050BC3HUA 4TXAD061BC3HUA 4TXAD064BC3HUA	TXA061C5 RXA061S3	24-1/2" Wide Furnaces	30 x 24-1/2 x 21-1/2

General Data

NON-BLEED TXV KITS	
Coils	R410A
4TXC, TXA - 018	4AYTXVH3D1831A
4TXC, TXA - 024	4AYTXVH3D1831A
4TXC, TXA - 025	4AYTXVH3D1831A
4TXC, TXA - 030	4AYTXVH3D1831A
4TXC, TXA - 031	4AYTXVH3D1831A
4TXC, TXA - 032	4AYTXVH3D3343A
4TXC, TXA - 036	4AYTXVH3D3343A
4TXC, TXA - 037	4AYTXVH3D3343A
4TXC, TXA - 042	4AYTXVH3D3343A
4TXC, TXA - 043	4AYTXVH3D3343A
4TXC, TXA - 044	4AYTXVH3D4863A
4TXC, TXA - 048	4AYTXVH3D4863A
4TXC, TXA - 049	4AYTXVH3D4863A
4TXC, TXA - 050	4AYTXVH3D4863A
4TXC, TXA - 060	4AYTXVH3D4863A
4TXC, TXA - 061	4AYTXVH3D4863A
4TXC - 063	4AYTXVH3D4863A
4TXC, TXA - 064	4AYTXVH3D4863A



General Data

PRODUCT SPECIFICATIONS^[1] 4 TXA-BC UNCASED UPFLOW / DOWNFLOW

	4TXAA018BC3HUA	4TXAA024BC3HUA	4TXAB025BC3HUA	4TXAB031BC3HUA	4TXAB032BC3HUA
INDOOR COIL--Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	2 / 18	2 / 18	3 / 14	3 / 14	3 / 14
Face Area (sq.ft.)	4.00	4.00	3.50	3.50	5.00
Tube Size (in.)	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections			-See Outline Drawings-		
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size (Gas) (in.)	5/8*	5/8*	5/8*	3/4	3/4
Line Size (Liquid) (in.)	5/16	5/16	5/16	3/8	3/8
DIMENSIONS (in.)	H x W x D	H x W x D	H x W x D	H x W x D	H x W x D
Crated (H x W x D)	18-1/2x17-1/2x26-1/2	18-1/2x17-1/2x26-1/2	16-1/2x20-1/2x 26-1/2	16-1/2x20-1/2 x26-1/2	22-3/4x20-1/2x26-1/2
Uncrated (H x W x D)			-See Outline Drawings-		
WEIGHT (lbs.)					
Shipping -- Net	21 / 19	21 / 19	24 / 22	24 / 22	32 / 29

	4TXAB036BC3HUA	4TXAC037BC3HUA	4TXAB042BC3HUA	4TXAC043BC3HUA	4TXAC044BC3HUA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 14	3 / 14	3 / 14	3 / 14	3 / 14
Face Area (sq.ft.)	5.00	5.00	5.00	5.00	6.00
Tube Size	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections			-See Outline Drawings-		
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	3/4*	3/4*	3/4*	3/4*	7/8*
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H x W x D	H x W x D	H x W x D	H x W x D	H x W x D
Crated (H x W x D)	22-3/4x20-1/2x26-1/2	22-3/4x24x26-1/2	22-3/4x 24 x 26-1/2	22-3/4x 24 x 26-1/2	28-1/4x24x26-1/2
Uncrated			-See Outline Drawings-		
WEIGHT (lbs)					
Shipping -- Net	32 / 29	33 / 30	32 / 29	33 / 30	38 / 34

	4TXAB048BC3HUA	4TXAC049BC3HUA	4TXAC060BC3HUA	4TXAD050BC3HUA	4TXAD061BC3HUA	4TXAD064BC3HUA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 14	3 / 14	3 / 14	3 / 14	3 / 14	3 / 18
Face Area (sq.ft.)	6.00	6.00	7.00	6.00	7.00	7.00
Tube Size	3/8	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections			-See Outline Drawings-			
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	7/8*	7/8*	7/8*	7/8*	7/8*	7/8*
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H x W x D	H x W x D	H x W x D	H x W x D	H x W x D	H x W x D
Crated (H x W x D)	28-1/4x20-1/2x26-1/2	28-1/4x24x26-1/2	31-1/2x27-1/2x26-1/2	28-1/4x27-1/2x26-1/2	31-1/2x27-1/2x26-1/2	31-1/2x27-1/2x26-1/2
Uncrated			-See Outline Drawings-			
WEIGHT (lbs)						
Shipping -- Net	36 / 33	38 / 34	44 / 40	39 / 35	45 / 41	45 / 41

* Reducer supplied with R-410A models

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240).
Refer to the Split System Outdoor product information site or www.ahrinet.org



General Data

PRODUCT SPECIFICATIONS^[1] – 4 TXC-BC - SPLIT SYSTEM HEAT PUMP / COOLING COMFORT™ COILS CASED UPFLOW / DOWNFLOW / HORIZONTAL

	4TXCA018BC3HCA	4TXCA024BC3HCA	4TXCB025BC3HCA	4TXCB031BC3HCA	4TXCB032BC3HCA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	2 / 18	2 / 18	3 / 14	3 / 14	3 / 14
Face Area (sq.ft.)	3.50	4.00	3.50	3.50	5.00
Tube Size	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections			-See Outline Drawings-		
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	1/2*	5/8*	5/8*	3/4	3/4*
Line Size -- Liquid (in.)	1/4	5/16	5/16	5/16	3/8
DIMENSIONS (in.)	H X W X D	H X W X D	H X W X D	H X W X D	H X W X D
Crated (H x W x D)	15-1/2x17-1/2x26-1/2	18-1/2x17-1/2x26-1/2	16-1/2x20-1/2x26-1/2	16-1/2x20-1/2x26-1/2	22-3/4x20-1/2x26-1/2
Uncrated			-See Outline Drawings-		
WEIGHT (lbs)					
Shipping -- Net	36 / 34	36 / 34	40 / 38	40 / 38	48 / 45

	4TXCB036BC3HCA	4TXCC037BC3HCA	4TXCB042BC3HCA	4TXCC043BC3HCA	4TXCC044BC3HCA	4TXCB048BC3HCA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 14	3 / 14	3 / 14	3 / 14	3 / 14	3 / 14
Face Area (sq.ft.)	5.00	5.00	5.00	5.00	6.00	6.00
Tube Size	3/8	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections			-See Outline Drawings-			
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	3/4*	3/4*	3/4*	3/4*	7/8*	7/8*
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H X W X D	H X W X D	H X W X D	H X W X D	H X W X D	H X W X D
Crated (H x W x D)	22-3/4x20-1/2x26-1/2	22-3/4x24x26-1/2	22-3/4x20-1/2x26-1/2	22-3/4x24x26-1/2	28-1/4x24x26-1/2	28-1/4x20-1/2x26-1/2
Uncrated			-See Outline Drawings-			
WEIGHT (lbs)						
Shipping -- Net	48 / 45	51 / 48	48 / 45	51 / 48	55 / 51	51 / 49

	4TXCC049BC3HCA	4TXCD050BC3HCA	4TXCC060BC3HCA	4TXCD061BC3HCA	4TXCD063BC3HCA	4TXCD064BC3HCA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 14	3 / 14	3 / 14	3 / 14	3 / 18	3 / 18
Face Area (sq.ft.)	6.00	6.00	7.00	7.00	7.00	7.00
Tube Size	3/8	3/8	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections		-See Outline Drawings-				
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	7/8*	7/8*	7/8*	7/8*	7/8*	7/8*
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H X W X D	H X W X D	H X W X D	H X W X D	H X W X D	H X W X D
Crated (H x W x D)	28-1/4x24x26-1/2	28-1/4x27-1/2x26-1/2	31-1/2x24x26-1/2	31-1/2x27-1/2x26-1/2	31-1/2x27-1/2x26-1/2	31-1/2x27-1/2x26-1/2
Uncrated		-See Outline Drawings-				
WEIGHT (lbs)						
Shipping -- Net	55 / 51	59 / 55	69 / 65	72 / 68	72 / 68	72 / 68

* Reducer supplied with R-410A models

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240).
Refer to the Split System Outdoor product information site or www.ahrinet.org



General Data

PRODUCT SPECIFICATIONS^[1] -- 4TXC-CC - HIGH EFFICIENCY STAGED SPLIT SYSTEM HEAT PUMP / COOLING COMFORT™ COILS CASED UPFLOW / DOWNFLOW / HORIZONTAL

	4TXCB003CC3HCA	4TXCB004CC3HCA	4TXCC005CC3HCA	4TXCC006CC3HCA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 18	3 / 18	3 / 18	3 / 18
Face Area (sq.ft.)	5.00	6.00	6.00	5.00
Tube Size	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections		-See Outline Drawings-		
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)*	5/8	3/4	3/4	5/8
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H X W X D	H X W X D	H X W X D	H X W X D
Crated (H x W x D)	22-3/4 x 20-1/2 x 26-1/2	28-1/4 x 20-1/2 x 26-1/2	28-1/4 x 24 x 26-1/2	22-3/4 x 24 x 26-1/2
Uncrated		-See Outline Drawings-		
WEIGHT (lbs)				
Shipping -- Net	48 / 45	52 / 49	55 / 51	51 / 48


	4TXCC007CC3HCA	4TXCC008CC3HCA	4TXCD009CC3HCA	4TXCD010CC3HCA
INDOOR COIL -- Type	PLATE FIN	PLATE FIN	PLATE FIN	PLATE FIN
Rows / F.P.I.	3 / 18	3 / 14	3 / 18	3 / 18
Face Area (sq.ft.)	6.00	7.00	7.00	7.00
Tube Size	3/8	3/8	3/8	3/8
Refrigerant Control (No internal check valve)	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV	Non-Bleed TXV
Drain Conn. Size (in.)	3/4 NPT	3/4 NPT	3/4 NPT	3/4 NPT
Duct Connections		-See Outline Drawings-		
REFRIGERANT CONNECTIONS	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED	R-410A BRAZED
Line Size -- Gas (in.)	3/4	3/4	3/4	3/4
Line Size -- Liquid (in.)	3/8	3/8	3/8	3/8
DIMENSIONS (in.)	H X W X D	H X W X D	H X W X D	H X W X D
Crated (H x W x D)	28-1/4 x 24 x 26-1/2	31-1/2 x 24 x 26-1/2	31-1/2 x 27-1/2 x 26-1/2	31-1/2 x 27-1/2 x 26-1/2
Uncrated		-See Outline Drawings-		
WEIGHT (lbs)				
Shipping -- Net	55 / 51	69 / 65	72 / 68	72 / 68

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240).
Refer to the Split System Outdoor product information site or www.ahrinet.org

Performance Data

PRESSURE DROP CHARACTERISTICS FOR COOLING AND HEAT PUMP COILS								
AIRFLOW (CFM) VS. PRESSURE DROP ACROSS WET COIL								
PRESSURE DROP (INCHES OF WATER COLUMN)								
MODEL	.05	0.1	0.15	0.2	0.25	0.3	0.35	0.4
4TXAA018BC3HUA 4TXCA018BC3HCA	360	545	690	820	930	1040	1135	1230
4TXAA024BC3HUA 4TXCA024BC3HCA	360	545	690	820	930	1040	1135	1230
4TXAB025BC3HUA 4TXAB031BC3HUA 4TXCB025BC3HCA 4TXCB031BC3HCA	310	515	700	865	1020	1170	1310	1450
4TXAB032BC3HUA 4TXAB036BC3HUA 4TXAB042BC3HUA 4TXCB032BC3HCA 4TXCB036BC3HCA 4TXCB042BC3HCA	480	690	860	1005	1130	1250	1360	1460
4TXAB048BC3HUA 4TXCB048BC3HCA	470	680	840	980	1110	1220	1330	1425
4TXAC037BC3HUA 4TXAC043BC3HUA 4TXCC037BC3HCA 4TXCC043BC3HCA	630	900	1105	1280	1440	1520	1710	1830
4TXAC044BC3HUA 4TXAC049BC3HUA 4TXCC044BC3HCA 4TXCC049BC3HCA	675	970	1200	1390	1560	1715	1860	2000
4TXAC060BC3HUA 4TXCC060BC3HCA 4TXCC008CC3HCA	680	965	1190	1375	1540	1685	1820	1950
4TXAD050BC3HUA 4TXCD050BC3HCA	810	1140	1390	1600	1790	1950	2110	2250
4TXAD061BC3HUA 4TXCD061BC3HCA	820	1155	1410	1620	1810	1980	2130	2280
4TXCD063BC3HCA	545	880	1135	1355	1550	1715	1875	2045
4TXAD064BC3HUA 4TXCD064BC3HCA 4TXCD009CC3HCA 4TXCD010CC3HCA	670	1000	1250	1470	1670	1850	2020	2180
4TXCB003CC3HCA	510	715	875	1005	1125	1230	1325	1415
4TXCB004CC3HCA	465	685	865	1015	1155	1280	1395	1505
4TXCC006CC3HCA	460	715	930	1115	1290	1450	1600	1740
4TXCC005CC3HCA 4TXCC007CC3HCA	550	820	1030	1210	1375	1525	1665	795

Outline Drawing for 4TXAA018BC3HUA, 4TXAC024BC3HUA, 4TXAB025BC3HUA, 4TXAB031BC3HUA, 4TXAB032BC3HUA, 4TXAB036BC3HUA, 4TXAB042BC3HUA, 4TXAB048BC3HUA, 4TXAC037BC3HUA, 4TXAC043BC3HUA, 4TXAC044BC3HUA, 4TXAC049BC3HUA, 4TXAC060BC3HUA, 4TXAD050BC3HUA, 4TXAD061BC3HUA, 4TXAD064BC3HUA (All dimensions are in inches)



MODEL	4TXAA018BC3HUA 4TXAA024BC3HUA	4TXAB025BC3HUA 4TXAB036BC3HUA	4TXAB032BC3HUA 4TXAB038BC3HUA 4TXAB042BC3HUA	4TXAB037BC3HUA 4TXAC043BC3HUA	4TXAB048BC3HUA	4TXAC044BC3HUA 4TXAC049BC3HUA	4TXAD050BC3HUA	4TXAC060BC3HUA	4TXAD061BC3HUA 4TXAD064BC3HUA
WEIGHT (LBS.)	19	22	29	30	33	34	35	40	41
REFRIGERANT CONTROL	TXV (NON-BLEED)								
HEIGHT "A" (IN)	17-3/8	15	21-1/4	20-3/4	25-5/16	24-15/16	24-3/8	29-1/8	28-9/16
OVERALL WIDTH "B" (IN)	13-1/4	16-1/4	16-1/4	19-3/4	16-1/4	19-3/4	23-1/4	19-3/4	23-1/4
OPENING WIDTH "C" (IN)	7-3/4	9	9	12-1/2	9	12-1/2	16	12-1/2	16
"D"	1-5/8	1	-	-	-	-	-	-	-
GAS CONNECTION	3/4 BRAZE	3/4 BRAZE	7/8 BRAZE	7/8 BRAZE	7/8 BRAZE	7/8 BRAZE	1-1/8 BRAZE	1-1/8 BRAZE	1-1/8 BRAZE
R40-A GAS REDUCER	5/8" X 3/4"	5/8" X 3/4" (025 ONLY)	3/4" X 7/8"	3/4" X 7/8"	3/4" X 7/8"	3/4" X 7/8"	7/8" X 1-1/8"	7/8" X 1-1/8"	7/8" X 1-1/8"
LIQUID CONNECTION	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE	5/16 BRAZE
DRAIN PAN	PLASTIC								

(All dimensions are in inches)

Front View Dimensions:

- Overall Width: 19-5/16
- Top Flange Width: 7/8
- Right Side Opening: 18-1/8
- Right Side Opening in Wrapper: 21-1/2
- Bottom Flange Width: 15/16
- Bottom Flange Depth: 2-1/2

Side View Dimensions:

- Overall Height: 14-7/16
- Top Flange Width: 1-3/4
- Top Flange Depth: 5-1/2
- Top Flange Offset: 1-3/16
- Top Flange Offset: 1-9/16
- Top Flange Offset: 3-5/8
- Top Flange Offset: 1-3/4

Labels and Connections:


- DUCT FLANGE
- SCHRAEDER VALVE
- GAS CONNECTION
- LIQUID CONNECTION
- PLUGGED SECONDARY DRAIN 3/4" NPT FOR HORIZONTAL POSITION
- PLUGGED PRIMARY DRAIN 3/4" NPT FOR HORIZONTAL POSITION
- PRIMARY DRAIN 3/4" NPT FOR VERTICAL POSITION
- PLUGGED SECONDARY DRAIN 3/4" NPT FOR VERTICAL POSITION
- Comfortwell
- P
- S

[illegible]

From Dwg. D342803 Rev1

Outline Drawing for 4TXCD050BC3HCA, 4TXCD061BC3HCA, 4TXCD063BCHCA, 4TXCD064BCHCA


(All dimensions are in inches)



MODEL	4TXCD050BC3HCA	4TXCD063BCHCA 4TXCD064BCHCA	4TXCD063BCHCA
WEIGHT (LBS)	55	68	73
REFRIGERANT CONTROL	TXV (NON-BLEED)		
HEIGHT "A" (IN)	26-7/8	30-1/16	
GAS CONNECTION	1-1/8 BRAZE		7/8 BRAZE
LIQUID CONNECTION	3/8 BRAZE		
MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED)	24-1/2		
DRAIN PAN	PLASTIC		

From Dwg. D342804


Outline Drawing for 4TXCB003CC3HCA, 4TXCB004CC3HCA, 4TXCC005CC3HCA, 4TXCC006CC3HCA, 4TXCC007CC3HCA, and 4TXCC008CC3HCA
(All dimensions are in inches)



MODEL	4TXCB003CC3HCAA	4TXCB004CC3HCAA	4TXCC005CC3HCAA	4TXCC006CC3HCAA	4TXCC007CC3HCAA	4TXCC008CC3HCAA
WEIGHT (LBS.)	45	49	48	51	65	
REFRIGERANT CONTROL	TXV (NON-BLEED)					
HEIGHT "A" (IN.)	22 - 5/8	26 - 7/8	22 - 5/8	26 - 7/8	30 - 1/16	
OVERALL WIDTH "B" (IN.)	17 - 1/2	17 - 1/2	21	21	21	
OPENING WIDTH "C" (IN.)	16 - 1/2	16 - 1/2	20	20	20	
TOP OPENING "D"	15 - 3/4	15 - 3/4	19 - 1/4	19 - 1/4	19 - 1/4	
GAS CONNECTION	5/8 BRAZE	3/4 BRAZE	5/8 BRAZE	5/8 BRAZE	3/4 BRAZE	
LIQUID CONNECTION	3/8 BRAZE					
MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED)	17 - 1/2					
DRAIN PAN	21					
	PLASTIC					

Outline Drawing for 4TXCD009CC3HCA and 4TXCD010CC3HCA

(All dimensions are in inches)



MODEL	4TXCD009CC3HCAA 4TXCD010CC3HCAA
WEIGHT (LBS.)	68
REFRIGERANT CONTROL	TXV (NON-BLEED)
HEIGHT "A" (IN.)	30-1/16
GAS CONNECTION	3/4 BRAZE
LIQUID CONNECTION	3/8 BRAZE
MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED)	24-1/2
DRAIN PAN	PLASTIC

From Dwg. D343415rev2



Notes



TRANE®

Trane
6200 Troup Highway
Tyler, TX 75707
www.trane.com

For more information contact
your local dealer (distributor)



Literature Order Number	22-1813-06
File Number	22-1813-06
Supersedes	22-1813-05
Date	05/10

Since **Trane** has a policy of continuous product improvement, it reserves the right to change design and specifications without notice.