



Type _____
 -09 -20

P4492

Catalog No.	Finish		Lamping	Dimensions (Inches)		
	Brushed Nickel	Antique Bronze		A	B	C
	P4492	-09		-20	9 (m) 100w	28-1/8



Specifications:

General

- Etched white inside glass shades (-09), Etched light umber glass shades (-20): 6" dia., 5" ht.
- Plated Brushed Nickel (-09) finish
- Painted Antique Bronze (-20) finish
- Steel construction
- Six feet of 9 gauge chain supplied.
- Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, Wall bracket, fixtures are available

Mounting

- Ceiling chain or stem mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Fixture can be mounted with the (2) 6" length stem or with chain or with a combination of stem and chain

Electrical

- Medium base ceramic sockets
- 15 feet of wire supplied
- Pre-wired

Labeling

- UL-CUL Dry location listed