


1560CB2 FLANGED ENDS 1562CB2 BUTT-WELD ENDS GLOBE CLASS 150 2"-8"



SPECIFICATIONS		
Design		API 600, ASME B 16.34
P-T Rating		ASME B 16.34
Connections		ASME B 16.5, 16.25
Face to Face		ASME B 16.10
Test & Inspection		API 598, RP 591
MATERIAL LIST		
ITEM	PARTS NAME	MATERIALS
		Unless otherwise specified
1	Body	A216 Gr WCB
2	Seat Ring/Facing	A105 / Co-Cr-W Face
3	Disc	A182 Gr F6a
4	Disc Nut	A182 Gr F6a
5	Stem	A182 Gr F6a
6	Gasket	Spiral Wound S/S w/ Graphite
7	Backseat Bushing	A276 Type 410
8	Bonnet	A216 Gr WCB
9	Packing	Graphoil w/ Braided Rings
10	Gland	A182 Gr F6a
11	Gland Flange	A105
12	Yoke Nut	A439 Type D2
13	Yoke Bushing	A47 Gr 32510
14	Handwheel	A47 Gr 32510
15	Lockwasher	A105
16	Handwheel Nut	Carbon Steel
17	Gland Eyebolt	Carbon Steel
18	Gland Eyebolt Nut	A307 Gr B
19	Body Bonnet Stud	A 193 Gr B7
20	Body Bonnet Stud Nut	A 194 Gr 2H
21	Gland Eyebolt Pin	Carbon Steel

DIMENSIONS

Size NPS	Nominal Size Dia. N INCHES (mm)	Line Flange						Height		Stem dv INCHES (mm)	Line Flange Bolts		Turns to Open	Hand- wheel Wd INCHES (mm)	Weight Approx. lbs (kg)
		Dia. D INCHES (mm)	Thickness (min.) b INCHES (mm)	Bolt Circle Dia. k INCHES (mm)	Hole Dia. d INCHES (mm)	Raised Face Dia. g INCHES (mm)	Face to Face BW L=L1 INCHES (mm)	Open H INCHES (mm)	Closed H INCHES (mm)		Quantity	Size INCHES (metric)			
2	2.00	6.00	0.62	4.75	0.75	3.62	8.00	14.01	12.44	0.88	4	5/8	8.4	8.00	53
	50.8	152.4	15.7	120.7	19.1	91.9	203.2	355.9	316.0	22.2	4	M16	8.4	203.2	24
2 1/2	2.50	7.00	0.69	5.50	0.75	4.12	8.50	14.05	12.48	0.88	4	5/8	8.4	9.00	70
	63.5	177.8	17.5	139.7	19.1	104.6	215.9	356.9	317.0	22.2	4	M16	8.4	228.6	32
3	3.00	7.50	0.75	6.00	0.75	5.00	9.50	17.20	15.02	1.00	4	5/8	8.4	9.00	86
	76.2	190.5	19.1	152.4	19.1	127.0	241.3	436.9	381.5	25.4	4	M16	8.4	228.6	39
4	4.00	9.00	0.94	7.50	0.75	6.19	11.50	20.78	18.02	1.13	8	5/8	10.8	10.00	120
	101.6	228.6	23.9	190.5	19.1	157.2	292.1	527.8	457.7	28.6	8	M16	10.8	254.0	55
6	6.00	11.00	1.00	9.50	0.88	8.50	16.00	24.45	20.91	1.25	8	3/4	16.5	12.00	222
	152.4	279.4	25.4	241.3	22.4	215.9	406.4	621.0	531.1	31.8	8	M20	16.5	304.8	101
8	8.00	13.50	1.12	11.75	0.88	11.00	19.50	28.00	24.00	1.38	8	3/4	22.0	18.00	344
	203.2	342.9	28.4	298.5	22.4	279.4	495.0	711.2	609.6	34.9	8	M20	22.0	457.2	156

Rev. 1

The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the most current information access www.milwaukeevalve.com

