

SPECIFICATION SHEET

Horizon Medicine Cabinet




FEATURES/TYPICAL SPECIFICATIONS

- · Recess Mount Installation
 - Wall Opening/Rough-in Dimensions:14" x 34" x 3½"
- Formed and welded steel housing (WB/ST)
 - 26 gauge steel with white, heat cured, acrylic paint finish
- Frameless mirror door
 - 5/32" thick float glass mirror door front with 1/2" beveled edge, 4 sides
 - 26 gauge steel door back with white, heat cured, acrylic paint finish
- 32" piano hinge is welded to the door and mechanically fastened to the cabinet body (HG01) (1 typical)
- Magnetic door catch in the cabinet body align to stainless steel striker plate on the door back (2 typical)
- Reversible for left-hand or right-hand door swing
- 3/16" thick float glass shelves, adjustable (ADJ) (3 typical)
- Includes installation hardware
- Standard Pallet Quantity of 28 units

Finishes:

Housing: PT01 - Basic White Mirror: 1/2" BVL - 1/2" Bevel Edge

Frame: Frameless



		Dimensions In Inches									
Model #	Description	Α	В	С	D	E	F	G	Н	J	K
868P34WHG	MEDCAB 1DR 16X36 FMLS WB/ST	16	36	1	4-1/2	13-1/2	1	15-1/2	33-1/2	1	1/4

REFERENCE	QTY.	REMARKS	Project				
			Location				
			Architect				
			Engineer				
			Contractor				
			Submitted by	Date			

^{*} All models and material specifications are subject to change or withdrawal without notice.

S868P34WHG_A