

NADYA

Features

- Solid brass construction
- Quarter-turn washerless ceramic disc valve cartridges
- Traditional lever handle design
- Spout assembly with integral supply hoses
- Spring-loaded, normally closed lever handle
- 6.53" (16.6 cm) spout height at outlet
- 4.82" (12.2 cm) spout reach (c-c)
- For single hole configurations

Hot and Cold Water Dispenser Faucet

107



Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAMPO/cUPC
- NSF/ANSI 61, SECTION 9
- NSF/ANSI 372
- IPC
- Energy Policy Act of 1992
- California Energy Commission
- All applicable US Federal and State material regulations



Colors / Finishes

- 10B: Oil Rubbed Bronze
 15: Polished Nickel
 15S: Satin Nickel PVD
 26: Polished Chrome
- Other: Refer to the Newport Brass catalog for additional color/finish options.

Specified Model		
Model	Description	Colors Finishes
107	Hot and Cold Water Dispenser Faucet	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other
5-036	Point-of-Use Water Heater (115V, 140°F to 190° range)	N/A

Product Specification Add "Color / Finish" suffix to Model number, below.

The Hot and Cold Water Dispenser Faucet shall be made of solid brass construction. Faucet shall incorporate a spout assembly with integral supply hoses and feature quarter-turn washerless ceramic disc valve cartridges. Faucet shall incorporate a traditional lever handle design and feature a spring-loaded, normally closed hot lever mechanism. Hot and Cold Water Dispenser Faucet shall have a 1.5 gallon (5.7 liters) per minute maximum flow rate and accommodate single hole configurations. Product shall incorporate a 6.53" (16.6 cm) spout height at outlet and a 4.82" (12.2 cm) spout reach (c-c). Hot and Cold Water Dispenser Faucet shall be Newport Brass Model 107/_____. [Point-of-Use Water Heater shall be Newport Brass Model 5-036].

107

PRODUCT DIMENSIONS (Units are in inches)

Product Dimensions are provided for reference only. For specific product installation guidelines, please reference the Installation Instructions of the product being installed.



