

Lead Free* **Model DCLF40 DOUBLE CHECK VALVE**

Job Name:	Contractor:
Job Location:	P.O. Number:
Engineer:	Representative:
Tag:	Wholesale Distributor:

SPECIFICATIONS

The Lead Free* Apollo® Model DCLF40 Double Check Valve assembly shall be prevent contamination of the potable water supply due to back-siphonage or backpressure from substances that are objectionable, but non-health hazards. The Apollo® domestic shut-off ball valves shall have stainless steel handles and made from Lead Free* materials.

OLY MADE

ISO 9001:2008

REGISTERED


FEATURES

- Lead Free* AB 1953 Certified
- · Corrosion resistant
- · Top-mounted test cocks for easy testing
- · Replaceable seats & reversible silicone seat discs
- MADE IN THE USA

MATERIAL SPECIFICATIONS

Part Name	Material
Body & Caps	UNS C89836 Lead Free* Bronze
Check Valve Seats	Glass-Filled Noryl®
Poppets	Glass-Filled Celcon
Springs	Stainless Steel
Seat Discs	Silicone

ORDERING INFORMATION



Y-STRAINER

□ 0 - None (Standard) □ 1 - With Y-Strainer SIZE

 \Box 5 – 1" □ 6 – 1 ¼" □ 7 - 1½" □ 8 - 2"

SHUT-OFF VALVES (Inlet x Outlet)

- ☐ 1 Less ball valves
- 2 With Apollo® ball valves
- 4 With union-end Apollo® ball valves

OPTIONS

- F SAE Test Cocks (3/4" 1" Standard)
- **LL** Locking Lever Handles (1 1/4" 2" Only)


APPROVALS

ASSE® 1015


PERFORMANCE RATING

Maximum Operating Pressure 175 psi Temperature Range 33 °F - 180 °F

Lead Free*: The wetted surfaces of this product shall contain no more than 0.25% lead by weighted average. Complies with AB 1953 and VT S.152. ANSI 3rd party certified and listed.



	101011	9 ()	***	<u> </u>	103.7
Size	3/4"	1"	1 1/4"	1 1/2"	2"
Α	13 ½	14	21 1/4	21 %	22 ¾
В	7 1/4	7 1/4	12 %	12 %	12 %
С	5 3/4	5 3/4	6 %	6 %	6 %
D	3	3 1/8	5	5	5 %
Wt.	8.5	10	26.5	26.5	32



FLOW CURVES

