

M Model DUXL, DUXLC AND DUXLM

Dielectric Pipe Fittings

Application

Ideal for use where Lead-Free* fittings are required. Designed for installation on potable water lines to protect against piping system deterioration caused by galvanic and stray current corrosion. A dielectric fitting is necessary where dissimilar metals are used in piping systems.

Standards Compliance

 Certified to NSF/ANSI 372 by IAPMO R&T* *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

Materials

Body Steel w/Zinc Coat Union Nut Steel w/Zinc Coat **Bolts and Nuts** Steel w/Zinc Coat Flanges (2-1/2" & 3") Cast Steel Tailpiece Low Lead Brass

Insulator Nvlon **EPDM** Gaskets

Steel w/Black Iron Oxide Coat Body (DUBI) Steel w/Black Iron Oxide Coat Tailpiece (DUBI) Union Nut (DUBI) Steel w/Black Iron Oxide Coat

Features

Sizes: 1/2", 3/4", 1", 1 1/4", 1 1/2", 2", 2 1/2", 3"

Maximum working water pressure (threaded fittings) 250 PSI Maximum working water pressure (flanged fittings) 175 PSI 180°F Maximum working water temperature

ANSI B 1.20.1 Thread connections Copper connections ANSI B 16.22

Dimensions & Weights (do not include pkg.)

FEMALE IRON PIPE BY FEMALE COPPER SOLDER JOINT									
PART NUMBER	DIMENSIONS							WEIGHT	
	INLET	OUTLET SIZE	Α .		В		WEIGHT		
	SIZE		in.	mm	in.	mm	lbs.	kg	
12-DUXLC	1/2"	1/2"	1 13/16	46	1	25	0.4	0.2	
34-DUXLC	3/4"	3/4"	2	51	1 1/4	32	0.5	0.2	
34-DUXL12C	3/4"	1/2"	1 13/16	46	1 1/4	32	0.5	0.2	
1-DUXLC	1"	1"	2 1/4	57	1 1/2	38	0.6	0.3	
114-DUXLC	1 1/4"	1 1/4"	2 13/32	61	1 7/8	48	0.8	0.4	
112-DUXLC	1 1/2"	1 1/2"	2 1/2	64	2 5/32	55	1.3	0.6	
2-DUXLC	2"	2"	2 15/16	75	2 25/32	71	2.5	1.1	
FLANGED FEMALE IRON PIPE BY FEMALE COPPER SOLDER JOINT									
212-DUXLC	2 1/2"	2 1/2"	3 5/8	92	6	152	13	5.9	
3-DUXLC	3"	3"	3 5/8	92	6 11/16	170	15	6.8	

MALE IRON PIPE BY FEMALE COPPER SOLDER JOINT								
PART	INLET	OUTLET	Α		В		WEIGHT	
NUMBER	SIZE	SIZE	in.	mm	in.	mm	lbs.	kg
12-DUXLM	1/2"	1/2"	2 3/4	70	13/16	21	0.5	0.2
34-DUXLM	3/4"	3/4"	3	76	1	25	0.6	0.3
34-DUXLM12C	3/4"	1/2"	2 3/4	70	13/16	21	0.7	0.3



MODEL DUXL



MODEL DUXLC (21/2" & 3")



XL LEAD FREE



MODEL DUXLC




MODEL DUXLM




Options

□ DUBI


Female iron pipe by female iron pipe with black iron oxide coating for gas service only (1/2"-2")




MODEL DUXL & DUBI



MODEL DUXLC (2 1/2" & 3")



MODEL DUXLC



MODEL DUXLM

DUXL - FEMALE IRON PIPE BY FEMALE BRASS PIPE									
DUBI - FEMALE IRON PIPE BY FEMALE IRON PIPE									
PART NUMBER	DIMENSIONS							WEIGHT	
	INLET	OUTLET	Α		В		WEIGHT		
	SIZE	SIZE	in.	mm	in.	mm	lbs.	kg	
12-DUXL/DUBI	1/2"	1/2"	2	51	1	25	0.5	0.2	
34-DUXL/DUBI	3/4"	3/4"	2 1/4	57	1 1/4	32	0.75	0.3	
1-DUXL/DUBI	1"	1"	2 1/2	64	1 1/4	32	1	0.5	
114-DUXL/DUBI	1 1/4"	1 1/4"	2 17/32	64.3	1 13/16	46	1.4	0.6	
112-DUXL/DUBI	1 1/2"	1 1/2"	2 15/16	75	2 3/16	56	3	1.4	
2-DUXL/DUBI	2"	2"	3	76	2 3/4	70	3.87	1.8	

Specifications

The Dielectric Union shall be certified to NSF/ANSI 372, rated for 250 psi (ANSI B 16.39). Flanged fittings shall be rated for 175 psi (ANSI B16.42 or B 16.24). The body and nut shall be steel with galvanized coat, the insulator shall be nylon, the tailpiece shall be low lead brass and the gaskets shall be EPDM. The Dielectric Union shall be a ZURN WILKINS Model DUXL, DUXLC or DUXLM.

Rev. C Zurn Industries, LLC | Wilkins Date: 11/19 1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766 Document No. DUXL-C-M Product No. Model DUXL-C-M Patent.zurn.com/patents

In Canada | Zurn Industries Limited 7900 Goreway Drive, Unit 10, Brampton, Ontario L6T 5W6, 877-892-5216 www.zurn.com