Cloroben (Main Snake®)

Drain Opener



FOR PROFESSIONAL USE ONLY
NOT FOR SALE TO OR USE BY CONSUMERS

DESCRIPTION

FOR PROFESSIONAL USE ONLY emergency drain opener. DRAIN SNAKE is a highly concentrated sulfuric acid drain opener. Heavier than water, it flows quickly to the blockage, opening drains and sewers clogged with almost any type of organic matter. These include such materials as paper, cloth, grease, sludge, soap, fat, sanitary products, wood, hair and all types of food. Can be used to thaw frozen lines as DRAIN SNAKE causes a significant rise in temperature when added to water. Will not harm septic systems or sewers when properly used for opening clogged drains. Can be used on metal or plastic. Contains corrosion inhibitor to help protect cast iron, steel, copper, brass or lead plumbing.

SIZES AND PACKING

STOCK NO.	SIZE	PACKING	WEIGHT/CASE
172001	1 qt.	12	50 lbs.
172002	1/2 gal.	6	49 lbs.

DRAIN SNAKE®

Drain Opener

APPROVALS AND LISTINGS

Not applicable.

SPECIFIC USES

Use **Cloroben DRAIN SNAKE** to disintegrate organic matter quickly to unclog drain or thaw frozen waste lines.

SPECIFIC APPLICATIONS*

DRAIN SNAKE can be used in septic or sewer waste systems.

DRAIN SNAKE may be used on cast iron, steel, copper, brass, lead and plastic pipe. **

PHYSICAL PROPERTIES

Boiling Point: 535°F
Melting Point: Liquid to -31°F
Solubility in Water: Completely
Odor: Slight

Appearance and color: Green Oily Liquid

WARNINGS OR CAUTIONS

- Do NOT use DRAIN SNAKE where other drain chemicals, hot water, or bleach are present.
- Do NOT allow DRAIN SNAKE to contact non-acid resistant enamel, stainless steel, chrome, aluminum and certain plastics.
- · Do NOT use plunger when DRAIN SNAKE is in drain.
- . Do NOT apply DRAIN SNAKE through garbage disposals.
- Avoid backup from drain opening by closing all connecting drains until this product is flushed from system.
- · Stand clear of drain openings immediately during and after use.
- . Do NOT get in eyes, on skin or on clothing.
- Do NOT breath vapors or mist.
- Wear heavy acid resistant gloves and goggles or face shield when handling.
- Keep container closed when not in use.
- Provide sufficient ventilation to prevent buildup and inhalation of vapors or mist.
- Do NOT add water or any other chemical to contents because of violent reaction.
- · Wash contaminated equipment, shoes and clothing thoroughly after handling.
- Cloroben DRAIN SNAKE is FOR PROFESSIONAL USE ONLY. Not for sale to or use by consumers.

FOR PROFESSIONAL USE ONLY NOT FOR SALE TO OR USE BY CONSUMERS



MATERIAL SAFETY INFORMATION

FOR MORE INFORMATION ON THIS PRODUCT, REQUEST MATERIAL SAFETY DATA SHEET (MSDS) #203

For Delivery by Fax	Call 1-800-942-4636	
Internet	See MSDS section of www.cloroben.com	
Mail	Contact Cloroben at address below or any Cloroben representative	

HMIS Hazard warning 3-0-2-H

INGREDIENTS	CAS#
Sulfuric Acid	7664-93-9

* For special applications which may not be covered on this or other Cloroben literature, please contact Cloroben Technical Services Department by phone at 1-800-221-9330 or send a fax to 1-800-333-3456.

DIRECTIONS FOR USE

- 1. Remove standing water from facility.
- 2. Determine **DRAIN SNAKE** dosage and stand time for type of facility from table below.
- Put on acid-resistant gloves and goggles or face shield. Stand clear of drain openings.
- 4. To open container, place on a flat surface. Hold bottle with one hand and unscrew cap taking care not to squeeze or tilt bottle.
- 5. Slowly pour a small amount of **DRAIN SNAKE** (less than 1/4 pint) DIRECTLY INTO DRAIN OPENING. Keep face and hands away from opening.
- If no "bubbling" or backup occurs, add rest of dosage slowly and carefully. Do NOT splash or spill DRAIN SNAKE outside of drain opening. Recap container tightly after use.
- After pouring DRAIN SNAKE into drain, immediately place inverted dishpan, bucket, or other deep container over drain opening to protect against possible eruption of drain contents and acid.
- 3. Allow to stand for recommended time before flushing.
- 9. Flush by adding one quart cold water. Wait 5 minutes. If line is clear, flush thoroughly with cold water.
- 10. Recommended dosages will open most lines and drains. If stoppage persists, repeat dosage, stand time and flush procedures.

FACILITY	DOSAGE	ALLOW TO STAND	<u> </u>
Small drains, waste lines & traps	1/2 pint	5 to 15 min.	
3" & 4" Lines	2 pints	15 to 30 min.	Frozen Lines- Repeat as needed.
6" & 8" Lines	1/2 gallon	15 to 30 min.	Grease Traps- Use grease dissolving Cloroben PT-4™
Urinals	1 pint	15 min.	Toilet Bowls- DO NOT use DRAIN SNAKE



CLOROBEN PRODUCTS

Hercules Chemical Company, Inc.

111 South Street, Passaic, NJ 07055-9100 Phone: 800-221-9330 • Fax: 800-333-3456

e-mail: cloro@herchem.com