



5 Max.

55.0

31

4 Mount holes each side details below

4 Accessory mount holes details below

68

55.0

80

294

12 IN WET WELL COVER

Model	Air Ports	Mount Holes & Accessory Mount Holes
124-100	G ³ / ₈	4 x M12 x 24 deep on 77.8 PCD 4 x M5 x 10 deep
127-100	3/ ₈ NPT	4 x 1/ ₂ UNC x 0.94" deep on 3.06" PCD 4 x 10-24 x 3/8" deep

- **Fail safe spring return units - clockwise or counter clockwise see pages 3-5**
- **Limit switch boxes for open/close indication - various switches for hazardous areas see pages 7-10**
- **AP pneumatic positioner - full range of options see pages 15/16**
- **EL electropneumatic positioner - full range of options see pages 13/14**
- **Integral solenoid valve see page 18**
- **P3 on/off positioner - full range of options including hazardous area see pages 19-21**
- **180° model see page 23/24**
- **Female drive and mounting details to DIN 3337 and ISO 5211 see page 48**
- **Spring to centre see page 22**
- **Geared manual override see page 44**
- **Code identification see page 57**
- **Torque outputs see pages 55/56**
- **See pages 48-50 for English dimensions and dimensions of spring options**
- **Accessory mount plate for positioners, switch boxes and clear cone monitor. See TD149.**
- **High Temperature / Low temperature options see page 47**

For further information
see General
Specification on
page 47.

