


Type \_\_\_\_\_

P4441

Ν	ıcı	ш.
 14		

			Dimensions (Inches)				
Catalog No.	Brushed Nickel	Antique Bronze	Lamping	Α	В	C	
P4441	-09	-20	5 (m) 100w	20-1/2	15	60	



## **Specifications:**

#### General

- White etched glass: 4" dia.
- 42" of 9 gauge chain supplied

•

Brushed Nickel (-09) plated Antique Bronze (-20) painted or acid

- Steel construction
- Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, fixtures are available

### **Mounting**

- Ceiling chain mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Threaded socket ring secures glass

### **Electrical**

- Medium base ceramic socket
- 96" feet of wire supplied
- Pre-wired

## <u>Labeling</u>

• UL-CUL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607



## Compact Fluorescent

## Gather **Energy Star compliant**

Chandeliers


Type

-09EBWB -20EBWB 

P4441

# **FINISH**

	Dalvad	n I I . A .!	Dimensions (In			nches)
Catalog No.	Brushed Nickel	Antique Bronze	Lamping	Α	В	C
P4441	-09EBWB	-20EBWB	5-13w GU24 CFL	20-1/2	15	60



## **Specifications:**

#### General

- White etched glass: 4" dia.
- 42" of 9 gauge chain supplied

**Brushed Nickel** (-09)plated Antique Bronze (-20)painted or acid

- Steel construction
- Five 13w GU24 CFL self-ballasted lamps (included)
- · Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, fixtures are available
- Energy Star Certified

### **Mounting**

- Ceiling chain mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Threaded socket ring secures glass

### Electrical

- GU24 base socket
- 96" feet of wire supplied
- Pre-wired

### <u>Labeling</u>

UL-CUL listed



**Progress Lighting** 701 Millennium Blvd. Greenville, South Carolina 29607