COPPER TUBING HANGERS



Fig. CT-65

Light Weight Adjustable Clevis

Size Range: 1/2" through 4"
Material: Carbon steel

Finish: \square Copper plated, also available in \square yellow dichromate and \square plastic coated.

Service: Recommended for suspension of non-insulated, stationary copper tube.

Approvals: Complies with Federal Specification WW-H-171-E (Type 12).

Installation:

- (1) Adjustment may be made either before or after tubing is in place without temporary support of pipe.
- (2) Hanger rod and nuts may be locked into position after adjustment by use of the upper nut.

Features: Provides for adjustment up to $1^{7}/8$ ".

Ordering: Specify nominal tube size, figure number, name and finish






FIG. CT-65: LOADS (LBS) • WEIGHT (LBS) • DIMENSIONS (IN)									
Tube Size	Max Load	Weight	Rod Size A	В	С	D	Rod Take Out - E	Adjustment F	
1/2	150	0.09	3/8	11/2	1 ²⁷ / ₃₂	1 7/ ₁₆	11/16	5/16	
3/4		0.10		1 ¹¹ / ₁₆	23/32	1 %16	11/4	7/16	
1	250	0.17		17/8	213/32	1%	17/16	1/2	
11/4		0.18		2 ⁵ / ₃₂	213/16	13/4	1 ¹¹ ⁄ ₁₆	5/8	
11/2		0.21		217/32	3%	1 ¹⁵ ⁄ ₁₆	21/16	13/16	
2		0.26		311/32	417/32	25/16	27/8	1 ³ ⁄ ₁₆	
21/2	350	0.48		3 ²⁷ / ₃₂	5%32	23/4	31/4	1 ⁵ ⁄ ₁₆	
3		0.55		4 ¹⁵ / ₃₂	67//32	3	37/8	15%	
4	400	0.60		431/32	631/32	31/4	43/8	17/8	

Note: Reflects changes in rod diameter from previously published data per recent revisions in MSS-SP-58 & 69

PROJECT INFORMATION	APPROVAL STAMP
Project:	☐ Approved
Address:	Approved as noted
Contractor:	☐ Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	