

Advanced Heating and Hot Water Systems

P.O. Box 429 · 120 Braley Road · East Freetown, MA 02717 · 508-763-8071 · Fax: 508-763-3769

Pioneer Heating
Appliance
Submittal Sheet

Pioneer Heating Appliance

rionosi riodanig Applianos	
JOB NAME:	
LOCATION:	
ARCH./ENGR.:	
WHOLESALER:	
MECH. CONTRACTOR:	
MODEL NUMBER:	
TYPE OF GAS:	
BTU/HR INPUT LOW – HIGH FIRE:	
NOTES:	
High Efficiency Heat Exchanger Copper Nickel primary with 800 H and Copper Nickel secondary tube construction Gasketless heat exchanger design Stainless Steel Buffer Tank with Built-in Dirt and Air Separation Tank construction of 304 L stainless steel System return tube with screen for built-in dirt and air separation	Additional Features: 12 year limited warranty Vents in PVC - CPVC - stainless steel – ULC S636 flexible polypropylene vent liner (chimney lining only) Field wiring connection board / Cascade wiring CAT 3 or 5 / Removal low voltage connector Built –in condensation system Manual reset high limit Dry contact for alarm output
 1 ¼" system return and supply connection Pressure relief port 	Ontional Faminance
 Top and bottom sensor 	Optional Equipment
Built-in low water cut-off probe	Outdoor Sensor (Part # 7250P-319)
Combustion System	Indirect Sensor (Part # 7250P-325)
 Modulating burner with up to 5 to 1 turndown 94% thermal efficiency (All Models) High-Grade Inconel premix burner 	System Sensor (Part # 7250P-324)
Spark ignition	2" PVC Concentric Vent Kit (Part # KGAVT0501CVT)
 Fires on Natural or LP Gas with included conversion kit Dual flame monitoring (Spark and Flame probe) Flame stabilization monitoring – Automatic adjustment of 	☐ 3" PVC Concentric Vent Kit (Part # KGAVT0601CVT)
firing rate to stabilize flame signal	2" Stainless Steel Outside Termination Vent Kit (Part # V500)
Integrated Control System	3" Stainless Steel Outside Termination Vent Kit (Part # V1000)
Digital operating control with LCD display three character for temperature and system monitor - LCD indicators for temperature for the control of the c	☐ 4" Stainless Steel Outside Termination Vent Kit (Part # V3000)
 appliance faults (red light) and operation (green light) System parameters password protected Outdoor reset with indirect priority 	☐ 6" Stainless Steel Outside Termination Vent Kit (Part # V4000)
 Multiple 120 volt 3 amp pump outputs – boiler pump and indirect pump 	☐ Condensate Neutralizer (Part # 7450P-212)
 0-10 volt input from a building management system Outdoor sensor input DHW sensor input 	☐ U.L. 353 Compliant Low Water Cut-Off Interface Kit w/ Manual Reset (Part # 7450P-225)
 Cascade up to 8 units Computer monitor cable allows user to monitor system 	☐ Alarm System to monitor any failure (Part # 7350P-602)
parameters – fault history – graphical monitor of system operation	☐ PC Connection Cable w / Software (Part # 7350P-320)

