



TECHNICAL SPECIFICATIONS



KDTS 3060

MODEL NUMBER 142006

DIMENSIONS: 59 7/8" x 30 1/8" x 77 1/2" Gelcoat



STANDARD FEATURES

- Four-piece gelcoated fiberglass tub-shower with PIN system for easy front installation
- Large top corner shelves, wide soap dish and standard acrylic handle (opt. metallic finishes)
- Right or left-hand drain
- Textured floor
- Optional unique features: Reinforced walls and grab bars
- Product also available in Above-the-Floor Rough
- Bottom bathing well: 44 1/8" L x 20" W
- 14 3/8 deep sump

UNIQUE FEATURES

- PIN system

OPTIONS

- In-line heater (factory-installed)
- Pump position opposite standard position
- Pre-assembled unit
- Back Wall reinforcement
- Left Wall reinforcement
- Right wall reinforcement

SYSTEMS

- Homestead

DOOR SELECTION

Combine with AKER's complete shower door offering visit www.akerbymax.com

CERTIFICATIONS

AKER products adhere to one or more of the following certifications:



Project :
 Contractor :
 AKER Representative : Tel :
 Date :

TECHNICAL SPECIFICATIONS




KDTS 3060


MODEL NUMBER 142006

TECHNICAL DRAWINGS


STANDARD




NO SYSTEM





NOT ABOVE-THE-FLOOR



ABOVE-THE-FLOOR




Whirlpool




REINFORCEMENT BACKING

OPTION 20212-L Shown
OPTION 20212-R Symetrical




OPTION 20212-B




GRAB BARS

OPTION 20203




OPTION 20204



OPTION

20203-20204



(▲) : Indicates Whirlpool jets positioning

(△) : Indicates suction positioning

All dimensions are approximate. Structure measurements must be verified against the unit to ensure proper fit.