

GATE 1152

BRONZE


125 lb. SWP-200 lb. WOG† • Industrial Service
Solid Wedge Disc • Rising Stem
Union Bonnet • Gland Packed • Threaded Ends

SPECIFICATIONS

1152	Conforms to: MSS SP-80. Type 2, Class 125, Threaded Ends.
------	--

MATERIAL LIST

NO.	PART	MATERIAL	SPECIFICATION
1	Body	Bronze	ASTM B 62
2	Bonnet	Bronze	ASTM B 62
3	Wedge Disc	Bronze	ASTM B 62
4	Stem	Bronze	ASTM B 62
5	Union Bonnet Nut	Bronze	ASTM B 62
6	Packing	Graphite	Commercial
7	Gland	Brass	ASTM B124 C37700
8	Packing Nut	Brass	ASTM B283 C37700
9	Handwheel	Mall. Iron	Commercial
10	Identification Plate	Aluminum	Commercial
11	Handwheel Nut	Brass	ASTM B 16



DIMENSIONS - INCHES / MILLIMETERS

Units	Size	A	B	C	C _v
Inches	1/4	1.75	5.13	2.00	5.6
mm	6.4	44.5	130.2	50.8	
Inches	3/8	1.88	5.13	2.00	10.7
mm	9.5	47.6	130.2	50.8	
Inches	1/2	2.13	5.50	2.50	17.6
mm	12.7	54.0	139.7	63.5	
Inches	3/4	2.25	6.25	2.75	32.0
mm	19.1	57.2	158.8	69.9	
Inches	1	2.56	7.19	2.75	54.0
mm	25.4	65.1	182.6	69.9	
Inches	1 1/4	2.75	8.56	3.13	97.0
mm	31.8	69.9	217.5	79.4	
Inches	1 1/2	3.25	9.63	3.50	135.0
mm	38.1	82.6	244.5	88.9	
Inches	2	3.63	11.75	4.00	230.0
mm	50.8	92.1	298.5	101.6	
Inches	2 1/2	4.50	14.50	4.75	337.0
mm	63.5	114.3	368.3	120.7	
Inches	3	4.88	16.75	5.25	536.0
mm	76.2	123.8	425.5	133.4	

† Non-Shock

Rev 5

INNOVATION IN EVERY VALVE



MILWAUKEE VALVE

The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com

www.milwaukeevalve.com