



Residential Power Vent High EF Energy Saver Gas Water Heater

The TTW® High EF FVIR Defender Safety System® Models Feature:

- Power Vented Water Heater—Designed for installations where atmospheric units cannot be used. Exhaust gases are vented under positive pressure directly out of the building through the roof or the wall.
- **ENERGY STAR® Qualified—**These models qualify for the September 1st, 2010 minimum ENERGY STAR® EF requirement, as well as most utility rebate programs.
- Honeywell Self Diagnostic Electronic Gas Control —Intelligent gas control with spark to pilot ignition system eliminates the constant burning pilot. This results in savings of pilot gas during stand by periods (120 V.A.C.).
 - Enhanced Performance—Proprietary algorithms provide enhanced First Hour Delivery ratings and tighter temperature differentials.
 - Advanced Temperature Control System—Microprocessor constantly monitors and controls burner operation to maintain accurate and consistent water temperature levels.
 - Intelligent Diagnostics—An exclusive green LED light prompts the installer during start-up and provides fifteen different diagnostic codes to assist in troubleshooting.
 - Pilot On Indication—Flashing green LED provides positive indication that pilot is on.
- Compatible With Optional Accessory Packages—Performance Package, Protection Package and Inlet Shut-Off Valve.
- Advanced ScreenLok® Technology Flame Arrestor Design—Flame arrestor is designed to prevent ignition of flammable vapor outside of the water heater.
- Flammable Vapor Sensor—Electronic sensor prevents burner operation if flammable vapors are detected. The sensor will also prevent operation if there is ongoing flammable vapor burn inside the combustion chamber.
- Maintenance Free—No regular cleaning of air inlet openings or flame arrestor is required under normal conditions.
- **Sight Window**—Offers a view into the combustion chamber to observe the operation of the pilot and burner.
- Factory installed Hydrojet® Total Performance System—Cold water inlet sediment reducing device helps prevent sediment build up in tank. This increases first hour delivery, while minimizing temperature build up at top of tank.
- Vitraglas® Lining—Bradford White tanks are lined with an exclusively engineered enamel formula that provides superior tank protection from the highly corrosive effects of hot water. This formula (Vitraglas®) is fused to the steel surface by firing at a temperature of over 1600°F (871°C).
- Powerful Blower Motor—Our significantly quiet design has greater resistance to outside winds and the power to vent in many difficult venting situations.
- Horizontal and Vertical Venting—With 2" or 3" PVC, ABS or CPVC (Maximum equivalent vent length on reverse side).
- 2" Non-CFC Foam Insulation—Covers the sides and top, reducing the amount of heat loss. This results in less energy consumption, improved operation efficiencies and jacket rigidity.
- Water Connections—3/4" NPT factory installed true dielectric fittings.
- Factory installed Heat Traps—Design incorporates a flexible disk that reduces heat loss in piping and eliminates the potential for noise generation.
- Protective Magnesium Rod.
- Pedestal Base
- T&P Relief Valve—Included.
- Low Restriction Brass Drain Valve—Durable tamper proof design.



Photo is of M-4-TW-40T6FBN

FEATURING:

















6 or 10-Year Limited Tank Warranties / 6 or 10-Year Limited Warranty on Component Parts.

For more information on warranty, please visit www.bradfordwhite.com For products installed in USA, Canada and Puerto Rico. Some states do not allow limitations on warranties. See complete copy of the warranty included with the heater.

Residential Power Vent Gas Water Heater

TTW® High EF Energy Saver Models NATURAL GAS AND LIQUID PROPANE GAS


Meet or exceed ASHRAE 90.1b (current standard) C.E.C. Listed 80% Recovery Efficiency


Model Number	Cap	acity				Rec 90°F	overy Rise*		A Floor to Vent	B Jacket Dia.	C Vent Size	D Floor to T&P	E Floor to	F Floor to	G Floor to	H Depth	Approx. Shipping Weight
	U.S. Gal.	lmp. Gal.	Nat. BTU/Hr. Input	LP BTU/Hr. Input	Nat. U.S. GPH	Nat. Imp. GPH	LP U.S. GPH	LP Imp. GPH	Conn. in.	in.	in.	Conn.	Gas Conn. in.	Top of Heater in.	Water Conn. in.	in.	lbs.
M-4-TW40T6FBN	40	33	40,000	38,000	43	36	41	34	67	20	2	50	113/4	563/4	573/4	247/8	152
M-4-TW50T6FBN	50	42	40,000	38,000	43	36	41	34	67	22	2	50	113/4	57	58	263/4	175
M-4-TW60T6FBN	60	51	40,000	38,000	43	36	41	34	68	24	2	501/2	113/4	573/4	583/4	283/4	210

Model Number	Capacity			Reco 50°C I		A Floor to Vent	B Jacket Dia.	C Vent Size	D Floor to T&P	E Floor to	F Floor to	G Floor to	H Depth	Approx. Shipping Weight
	Liters	Nat. kW Input	LP kW Input	Nat. Liters/ Hour	LP Liters/ Hour	Conn. mm.	mm.	mm.	Conn. mm.	Gas Conn. mm.	Top of Heater mm.	Water Conn. mm.	mm.	kg.
M-4-TW40T6FBN	151	11.7	11.0	163	155	1702	508	51	1270	298	1441	1467	632	69
M-4-TW50T6FBN	190	11.7	11.0	163	155	1702	559	51	1270	298	1448	1473	679	80
M-4-TW60T6FBN	227	11.7	11.0	163	155	1727	610	51	1283	298	1467	1492	730	96

Propane models feature a Titanium Stainless Steel propane burner. For Propane (LP) models change suffix "BN" to "SX" For 10 year models, change suffix from "6" to "10".

¹¹⁰ V.A.C. Required for Power Venting / 110 V.A.C., 60HZ, 3.1 Amperes





M-4-TW40 M-4-TW50 M-4-TW60	2" Vent Pipe	3" Vent Pipe			
Max. Equivalent Leng	†50 ft.	†120 ft.			
Min. Equivalent Leng	7 ft.	15 ft.			
Number	45 ft.	115 ft.			
of	2	40 ft.	110 ft.		
90° Elbows	35 ft.	105 ft.			

†For high altitude installations, consult the installation instructions.

General

All gas water heaters are certified at 300 PSI (2068 kPa) test pressure and 150 PSI (1034 kPa) working pressure. All water connections are 3/4" NPT (19mm) on 8" (203mm) centers, all gas connections are 1/2" (13mm). All models design certified by CSA International (formerly AGA/CGA), ANSI Z-21.10.1 and peak performance rated.

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.

Suitable for Water (Potable) Heating and Space Heating.

Toxic chemicals, such as those used for boiler treatment, shall NEVER be introduced into this system. This unit may NEVER be connected to any existing heating system or component(s) previously used with a non-potable water heating appliance.



For U.S. and Canada field service, contact your professional installer or local Bradford White sales representative.

Sales 800-523-2931 • Fax 215-641-1670 / Technical Support 800-334-3393 • Fax 269-795-1089 • Warranty 800-531-2111 • Fax 269-795-1089 International: Telephone 215-641-9400 • Telefax 215-641-9750 / www.bradfordwhite.com

BRADFORD WHITE-CANADA* INC. Sales / Technical Support 866-690-0961 / 905-238-0100 • Fax 905-238-0105 / www.bradfordwhite.com

Built to be the Best™

©2011, Bradford White Corporation. All rights reserved.

258-B-0211-A Printed in U.S.A

^{*}Based on manufacturer's rated recovery efficiency.