




Compact Fluorescent

Wisten

Directionals

Catalog No.	Finish		Lamping	Dimensions (Inches)	
	Brushed Nickel	Antique Bronze		A	B
P3361	-09	-20	3-18w GU-24	19-7/16	19-7/16



### Specifications:

#### General

- Etched glass shades: 3-13/16" dia., 5-3/16" ht.
- Plated Brushed Nickel (-09) finish
- Painted Antique Bronze (-20) finish
- Steel construction
- Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Sconce, fixtures are available

#### Mounting

- Wall or ceiling mount
- Ceiling pan covers a standard 4" hexagonal recessed outlet box: 11" dia., 1" deep
- Mounting strap for outlet box included

#### Electrical

- GU24 base sockets
- Threaded socket ring secures glass
- Pre-wired

#### Labeling

- cCSAus Damp location listed

Progress Lighting  
701 Millennium Blvd.  
Greenville, South Carolina  
29607

www.progresslighting.com

Rev. 09/13