


Type _____

-09 -77

P4288 ☐ ☐

| Catalog No. | Finish | | Lamping | Dimensions (Inches) | | |
|-------------|----------------|---------------|------------|---------------------|----|-----|
| | Brushed Nickel | Forged Bronze | | A | B | C |
| P4288 | -09 | -77 | 9 (m) 100w | 31-1/2 | 32 | 155 |


Specifications:
General

- Swirled etched (-09), Frosted caramel swirl (-77) glass trumpet shaped shades: 7" dia., , 5-3/4" ht.
- Scroll arms
- Steel construction
- Six feet of 9 gauge chain supplied.
- Plated Brushed Nickel (-09) finish
- Hand painted Forged Bronze (-77) finish
- Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, fixtures are available

Mounting

- Ceiling chain mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- Medium base ceramic sockets
- 15 feet of wire supplied
- Pre-wired

Labeling

- UL-CUL listed