# 59LF-300 Series

Model YBS-LF - Bronze Wye-Strainer

## LEAD FREE

# SUBMITTAL SHEET







## **DESCRIPTION**

The Apollo® Lead Free\* YBS-LF (59LF-300) Series Heavy Pattern Strainers are designed with large area screens to protect piping systems and process equipment from unwanted foreign particles with minimum pressure loss.

#### **FEATURES**

- · EZ-Solder™ Lead Free\* Bronze
- · 100% Factory Pressure Tested
- · Self-Aligning Screen Design
- Numerous Mesh and Blowoff Options including Blowoff Ball Valves
- · ARRA Compliant
- · 100% Cast, Machined and Assembled in the USA

#### **APPROVALS**

· NSF/ANSI - 372 Lead Free

#### PERFORMANCE RATING

- · Working Pressure (Non-Shock):
- 400 PSIG @ 150°F
- · Max Temperature: 450°F

#### **MODELS**

- (59LF000) Female NPT Connection
- (59LF300) Solder Connection (1/2"-3")

#### **OPTIONS**

- · (-E1) 20 Mesh
- · (-A1) 40 Mesh
- (-01) Plain Cap
- · (-B1) 60 Mesh
- · (-C1) 80 Mesh
- (-H1) 100 Mesh
- (-02) Tapped Cap
- · (-P2) Tapped Cap with Plug
- · (-06) Tapped cap with Ball Valve (3/4" 2" Only)

#### STANDARD MATERIALS LIST

Cast Bronze, ASTM Lead Free B584
.ead Free Brass, JNS C27450 (1/8" - 1") .ead Free Brass, \STM B584 C89836 (1-1/4" - 4")
Stainless Steel, 304
PTFE
PTFF

## **DIMENSIONS**

MODEL NUMBER	PART NUMBER	SIZE (IN.)	LENGTH (IN.)	(-02 SUFFIX)	NET SCREEN AREA (IN²)	WT. (LB.)
YBS12LF	59LF-303	1/2	2.75	1/4 NPT	3.2	0.50
YBS34LF	59LF-304	3/4	4.00	1/2 NPT	6.7	1.21
YBS1LF	59LF-305	1	4.75	3/4 NPT	10.8	1.89
YBS114LF	59LF-306	1-1/4"	5.25	3/4 NPT	13.5	2.80
YBS112LF	59LF-307	1-1/2	6.00	1 NPT	19.0	4.26
YBS2LF	59LF-308	2	7.25	1-1/4 NPT	27.6	6.27
YBS212LF	59LF-309	2-1/2	9.58	1-1/4 NPT	41.0	11.17
YBS3LF	59LF-310	3	10.58	1-1/2 NPT	56.0	16.48

# 

PRESSURE LOSS (PSI)

## STANDARD SCREENS

SIZE (IN.)	SCREEN
1/2	50 Mesh
3/4 to 3	20 Mesh